







SWITCH SCHEMATIC
LATCHING



PCB MOUNTING

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT RATING: 0.1A MAX. @ 28VDC
- ▲ 5. CONTACT MATERIAL: GOLD
6. ELECTRICAL LIFE: 200,000 Typical
7. OPERATING LIFE: 200,000 CYCLES Typ.
8. OPERATING TEMP: -40°C to +85°C
9. OPERATING FORCE: 300 $\pm$ 150 gf
10. CONTACT RESISTANCE: 100 MILLI-OHM INITIAL TYP. MAX.
11. DIELECTRIC STRENGTH: 1000 VAC FOR 1 MINUTE
12. TRAVEL TO MAKE: 2.20mm $\pm$ 0.2 LATCHING
13. 2011/65/EU (ROHS) COMPLIANT
14. ▲ DENOTES CRITICAL PARAMETER
- ▲ 15. LED COLOR: RED: 1 CHIP, 2.1-2.5 VDC@20mA
GRN: 1 CHIP, 3.2-4.0 VDC@20mA
BLU: 1 CHIP, 3.1-3.8 VDC@20mA



C	22858	update Note 15	5/23/17	MW
B	22350	SHOW "E" ON BOTTOM VIEW	6/16/16	MW
A	22320	RELEASED FOR PRODUCTION	5/31/16	MJR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE ULP22EEP1RSFCL1RGB

SCALE 3:2

DATE 5/31/2016

DR MJR

DWG B800075

REV C