


SPECIFICATIONS:

ELECTRICAL:

CURRENT RATING:	1 AMPS
INSULATION RESISTANCE:	1,000 MΩ MIN. @ 500 VDC
DIELECTRIC WITHSTANDING VOLTAGE:	1,000 VAC FOR 1 MINUTE
CONTACT RESISTANCE:	30 mΩ MAX.
OPERATING TEMPERATURE:	-55°C TO +105°C

MATERIALS:

INSULATION:	PBT, UL94 V-0 RATED
CONTACTS:	PHOSPHOR BRONZE
CONTACT PLATING:	GOLD FLASH IN MATING AREA
SHELL:	BRIGHT TIN IN SOLDER AREA STEEL, NICKEL PLATED



111-YYY-103L001

SERIES
POSITIONS014
024
036
050

GENDER

1 = MALE

TERMINATION

0 = SOLDER CUP

SHELL PLATING

3 = NICKEL

HARDWARE

00 = NO HARDWARE

PLATING

1 = GOLD FLASH

WILL ACCEPT 26-20 AWG WIRE

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.


DRAWN:
WAYNE ROBBINS
DATE:
01/16/2019

UNITS = mm


DO NOT SCALE FROM DRAWING

NorComp


SCALE: NTS	1	2	REV 15
DWG NO.			111-YYY-103L001




14 POSITION



36 POSITION



24 POSITION



50 POSITION

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS
DATE:
01/16/2019

UNITS = inch

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 2	OF 2	REV 15
DWG NO. 111-YYY-103L001			