



SPECIFICATIONS:

ELECTRICAL:

INSULATION RESISTANCE: 5,000 MΩ MIN.
 DIELECTRIC WITHSTANDING VOLTAGE: 1,000 VAC FOR 1 MIN
 CURRENT RATING: 5 AMPS
 WORKING VOLTAGE: 250V
 OPERATING TEMPERATURE: -55°C TO +105°C

MATERIALS:

CONTACTS: GOLD PLATED COPPER ALLOY
 INSULATOR: PA9T UL94 V-0 RATED
 SHELL: 260° PROCESS TEMP MAX
 BRACKET: NICKEL PLATED STEEL
 BOARD LOCK: NICKEL PLATED ZINC ALLOY
 SCREW LOCK: TIN PLATED COPPER ALLOY
 NICKEL PLATED COPPER ALLOY

179-YYY-613R571

SERIES
POSITIONS
009
015
025
037

HARDWARE OPTIONS

57 = 4-40 STAND OFFS/BOARD LOCKS

PLATING OPTIONS

1 = GOLD FLASH (ENTIRE CONTACT)
 A = 30μ" GOLD MATING AREA/GOLD FLASH TAILS
 9 = 30μ" GOLD MATING AREA/TIN TAILS

DIMENSIONS(mm)

SIZE	A ±.38	B ±.25	C ±.38
9	30.81	24.99	12.55
15	39.19	33.32	12.55
25	53.04	47.04	12.55
37	69.32	63.50	12.55

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
 THE PROPERTY OF NorComp AND SHALL NOT
 BE REPRODUCED, COPIED OR USED AS THE
 BASIS FOR THE MANUFACTURE OR SALE OF
 APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
 C. SMITH

DATE:
 03/30/2007

UNITS = mm [inch]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	1	1	REV 6
DWG NO. 179-YYY-613R571			