


NUMBER OF CONTACTS	"A" Inch (mm)	"B" Inch (mm)	"C" Inch (mm)	"D" Inch (mm)	"E" Inch (mm)
15	1.213 (30.80)	.984 (24.99)	.666 (16.92)	.090 (2.29)	.756 (19.20)
26	1.543 (39.20)	1.312 (33.32)	.970 (24.65)	.090 (2.29)	1.091 (27.70)
44	2.087 (53.00)	1.852 (47.04)	1.512 (38.40)	.090 (2.29)	1.618 (41.10)
62	2.732 (69.40)	2.500 (63.50)	2.157 (54.80)	.095 (2.41)	2.256 (57.30)
78	2.638 (67.00)	2.406 (61.10)	2.079 (52.81)	.095 (2.41)	2.169 (55.10)

NOTE:

MATERIAL	
HOUSING:	PBT UL94V-0, BLACK
	230°C PROCESS TEMP
CONTACT:	COPPER ALLOY
SHELL:	STEEL
FINISH	
CONTACT:	FULL GOLD FLASH
SHELL:	NICKEL
ELECTRICAL	
RATED CURRENT:	3A
DWV:	500VAC RMS FOR 1 MIN
INSULATOR RESISTANCE:	1000 MΩhms MIN.
CONTACT RESISTANCE:	15 mΩhms MAX.
ENVIRONMENT	
OPERATION TEMPERATURE:	-50°C TO +100°C



SERIES _____ 197-YYY-Y13LYY1

NUMBER OF CONTACTS _____

GENDER _____

1 = MALE

2 = FEMALE (NO GROUND INDENTS)

PC MOUNT _____

3 = NICKEL SHELL _____

HARDWARE OPTIONS: _____

00 = .120 MOUNTING HOLE

55 = 4-40 CLINCH NUT (CN)

03 = 4-40 CLINCH NUT (CN) && 4-40 JACK SCREW


PLATING: _____

1 = GOLD FLASH

00 THRU HOLE

55 CN

03 CN // JACK SCREW



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS

DATE:
09/15/2005

UNITS = inch (mm)

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET
1 OF
1

REV
6

DWG NO.

197-YYY-113LYY1