


NUMBER OF CONTACTS	"A" Inch (mm)	"B" Inch (mm)	"C" Inch (mm)	"D" Inch (mm)	"E" Inch (mm)
15	1.213 (30.80)	.984 (24.99)	.643 (16.34)	.090 (2.29)	.756 (19.20)
26	1.543 (39.20)	1.312 (33.32)	.972 (24.70)	.090 (2.29)	1.091 (27.70)
44	2.087 (53.00)	1.852 (47.04)	1.512 (38.40)	.090 (2.29)	1.618 (41.10)
62	2.732 (69.40)	2.500 (63.50)	2.157 (54.80)	.095 (2.41)	2.256 (57.30)
78	2.638 (67.00)	2.406 (61.10)	2.055 (52.20)	.095 (2.41)	2.169 (55.10)



NOTE:

MATERIAL
HOUSING:PBT UL94V-0, BLACK
230°C PROCESS TEMPCONTACT:
SHELL:COPPER ALLOY
STEELFINISH:
CONTACT:FULL GOLD FLASH
NICKELELECTRICAL:
RATED CURRENT:3A
500VAC RMS FOR 1 MINDWV:
INSULATOR RESISTANCE:

1000 MΩhms MIN.

CONTACT RESISTANCE:

15 mΩhms MAX.

ENVIRONMENT:
OPERATION TEMPERATURE:

-50°C TO +100°C

197-YYY-Y13LYY1

SERIES _____

NUMBER OF CONTACTS _____

GENDER _____

1 = MALE
2 = FEMALE (NO GROUND INDENTS)

PC MOUNT _____

3 = NICKEL SHELL _____

HARDWARE OPTIONS: _____

00 = .120 MOUNTING HOLE

55 = 4-40 CLINCH NUT (CN)

03 = 4-40 CLINCH NUT (CN) && 4-40 JACK SCREW

PLATING: _____

1 = GOLD FLASH

RoHS COMPLIANT

UNITS = inch (mm)

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

P. JENKINS

DATE:

09/15/2005

NorComp

SCALE: NTS SHEET 1 OF 1 REV 6

DWG NO.

197-YYY-213LYY1