

SPECIFICATIONS:

MATERIALS:




HOUSING: PBT, UL94 V-0, BLACK
 SHELL: NICKEL PLATED STEEL
 HARDWARE: NICKEL PLATED BRASS

ELECTRICAL:

RATED VOLTAGE: 250V
 INSULATION RESISTANCE: 5 Gohms MIN.
 DIELECTRIC WITHSTANDING: 1,000 VAC r.m.s.

ENVIRONMENT:


OPERATING TEMPERATURE: -55°C TO +125°C



SIGNAL AND POWER CONTACTS SOLD SEPARATELY
 (5x) SIGNAL CONTACT P/N = 680M002-071LY0Y (Y = Place holder for variants)
 (4x) POWER CONTACT P/N = 680M002-072LY0Y (Y = Place holder for variants)

680M9W4273L0Y0

0 = NO HARDWARE
 1 = 2.5mm #4-40 CLINCH NUT PCB SIDE
 2 = 2.5mm M3 CLINCH NUT PCB SIDE



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
 THE PROPERTY OF NorComp AND SHALL NOT
 BE REPRODUCED, COPIED OR USED AS THE
 BASIS FOR THE MANUFACTURE OR SALE OF
 APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
 J. KADEL

DATE:
 11/16/2022

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 1 OF 1	REV 1
DWG NO. 680M9W4273L0Y0		