



DESCRIPTION: 2B // QUIK-LOQ // M // CABLE MOUNT // SOLDER CUP



822BYYY-173LYY1

SERIES _____
POSITIONS _____
YYY = SEE POSITION CHART
GENDER _____
1 = MALE
TYPE _____
7 = CABLE MOUNT
KEY ORIENTATION (SEE KEY ORIENTATION CHART) _____
3 = 1 KEY // 0°
A = 2 KEYS // 30°
COLLET SIZE _____
YY = SEE COLLET SIZE CHART
CONTACT PLATING _____
1 = 7μ" GOLD PLATED

KEY ORIENTATION CHART	
KEY ORIENTATION	DIAGRAM
3	
A	

COLLET SIZE CHART	
COLLET SIZE:	CABLE DIAMETER:
50	4.30 ~ 5.20
60	5.30 ~ 6.20
70	6.30 ~ 7.20
80	7.30 ~ 8.20
90	8.30 ~ 9.20
00	9.30 ~ 10.20

SPECIFICATIONS:

MATERIALS:

SHELL & COLLET NUT:	BRASS, 196u" CHROME PLATED MIN.
CONTACTS:	7u" GOLD PLATED BRASS OVER 196u" NICKEL MIN.
INSULATOR:	PPS (HIGH TEMPERATURE)
STRAIN RELIEF (BOOT):	THERMOPLASTIC POLYURETHANE

MECHANICAL:

MATING CYCLES:	5000 CYCLES
OPERATING TEMPERATURE:	-40°C TO +200°C
PROCESS TEMPERATURE:	260°C FOR 5 SECONDS
SHIELDING:	75dB @ 10MHz // 40dB @ 1GHz
IP RATING:	50
MAX TORQUE VALUE:	2.5 Nm

POSITION CHART // ELECTRICAL/WIRE SPECIFICATIONS

*solder side view of insulator

POSITIONS	CONTACTS*	CONTACT Ø	MAX CONTACT mΩ	WORKING VOLTAGE	MAX AMPERAGE	MAX WIRE AWG
002		2.00mm	3.0 mΩ	700 V	20.5 A	16
003		1.60mm	4.0 mΩ	800 V	17.0 A	18
004		1.30mm	5.0 mΩ	610 V	15.0 A	20
006		1.30mm	5.0 mΩ	450 V	12.0 A	20
008		0.90mm	6.0 mΩ	500 V	10.0 A	22
010		0.90mm	6.0 mΩ	500 V	8.0 A	22
012		0.70mm	7.5 mΩ	480 V	7.0 A	24
014		0.70mm	7.5 mΩ	380 V	6.5 A	24
016		0.70mm	7.5 mΩ	315 V	6.0 A	24
019		0.70mm	7.5 mΩ	315 V	5.0 A	24
026		0.50mm	10.0 mΩ	315 V	1.5 A	28

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:
02/03/2016

NorComp

SCALE:
NTS

SHEET 1 OF 1

REV
10

DWG NO.

822BYYY-173LYY1