

SPECIFICATIONS:

MATERIALS:

HOUSING:	PBT, UL94 V-0, BLACK
CONTACTS:	10 μ " GOLD PLATED BRASS
NUT:	NICKEL PLATED BRASS
SHELL:	NICKEL PLATED BRASS
X-SHELL:	NICKEL PLATED Zn ALLOY
ORING:	EPDM




ELECTRICAL:

RATED CURRENT:	0.5A
RATED VOLTAGE:	50VAC/60VDC
INSULATION RESISTANCE:	100 M Ω ms MIN.
CONTACT RESISTANCE:	10 m Ω ms MAX.


ENVIRONMENT:

OPERATING TEMPERATURE:	-40°C TO +85°C
WATER PROOF:	IP67

MAX WIRE AWG:	26 AWG
---------------	--------



NUT



RECOMMENDED PANEL CUT-OUT

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:

12/11/2023

SCALE:

NTS

SHEET 1 OF 1

REV

0

DWG NO.

859-X08-103R004

NorComp