

## SPECIFICATIONS:

## MATERIALS:



HOUSING:	PA9T, UL94 V-0, BLACK
CONTACTS:	GOLD FLASH PLATED BRASS
GROUND:	NICKEL PLATED PHOSPHOR BRONZE
ORING:	VITON
CAP:	PA66

## ELECTRICAL:



RATED CURRENT:	2A
RATED VOLTAGE:	30V
INSULATION RESISTANCE:	100 M $\Omega$ ms MIN.
CONTACT RESISTANCE:	10 m $\Omega$ ms MAX.

## ENVIRONMENT:

OPERATING TEMPERATURE:	-40°C TO +85°C
WATER PROOF:	IP67 (Mated Condition)



Component side (front view)  
Recommended keepout area on the circuit board



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
J. KADEL

DATE:  
03/18/2024


UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:	NTS	1	2	REV
DWG NO.				1

862-008-113R001



The tape size complies with the (EIA-481-D) specification requirements.

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
J. KADEL  
DATE:  
03/18/2024

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 2 OF 2	REV 1
DWG NO. 862-008-113R001		