


SPECIFICATIONS:

MATERIALS:


SHELL: NICKEL PLATED BRASS
ORING: EPDM
NUT: NICKEL PLATED BRASS

ENVIRONMENT:

OPERATING TEMPERATURE: -40°C TO +85°C
WATER PROOF: IP67 (Mated Condition)



Panel Cut Out Recommendation



INSERT CONNECTOR MATING END HERE

MOUNT NUT TO PANEL FIRST BEFORE
INSERTING CONNECTOR. WHEN
INSERTING CONNECTOR, ENSURE NUT
IS PUSHED FULLY ONTO CONNECTOR.

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:
03/18/2024

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 1	OF 2	REV 0
---------------	------------	---------	----------

DWG NO.
862-M-SHELL