



DESCRIPTION: 970 SERIES D-SUB BACKSHELL



* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS: ANGLE $\pm 1^\circ$
UNIT: MM .XX ± 0.35

DIMENSIONS(mm/in)				
SIZE	A $\pm .50$ 0.02	B $\pm .50$ 0.02	C $\pm .50$ 0.02	D $\pm .25$ 0.01
50	67.50	54.00	18.70	61.00
	2.657	2.126	0.736	2.402

BACKSHELL MATERIAL: DIE-CAST ZINC ALLOY
PLATING: NICKEL
JACKSCREWS: STEEL:ZN PLATED
M3 HOODSCREWS: STEEL:ZN PLATED
CLAMP SCREWS: STEEL:ZN PLATED
METAL CLAMP: STEEL:NICKEL PLATED
COMPRESSION INSERT: ABS, UL 94-HB, BLACK COLOR
OPERATING TEMP: -40°C TO +120°C

BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (2) 4-40 THUMBScrews
- (2) HOUSING SCREWS
- (2) CLAMP SCREWS
- (1) METAL CLAMP
- (1) SET OF COMPRESSION INSERTS—VARIOUS SIZES
DIAMETERS 11mm(.433"), 12.5mm(.492"), 14mm(.551"), 15mm(.591")
& 17mm [0.669"] (WITHOUT GROMMET)

**NOTE: 3 in-lbs IS RECOMMEND TORQUE FOR HOUSING SCREWS

970-050-030R121
 SERIES 970
 POSITIONS 050
 MATERIAL 030 = ZINC ALLOY
 COLOR 12 = NICKEL OVER COPPER
 PUT-UPS 1 = KIT

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON
DATE:
04/23/2012

UNITS = "as specified"

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	1	1	REV 1
DWG NO. 970-050-030R121			