






- 1. ALL DIMENSIONS IN MM [INCH]
- 2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- 3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
- 5. RATING: 3A 250 VAC cUL
- 6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
- 7. MECHANICAL LIFE: 1,000,000 CYCLES.
- 8. INSULATION RESISTANCE: 1,000 M Ω @ 500VDC MIN.
- 9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
- 10. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
- 11. OPERATING TEMP.: -20°C to 55°C
- 12. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 13. LAMP VOLTAGE: 20mA 24V
- 14. TRAVEL: 3.2mm
- 15. ACTUATION FORCE: 2.5 ± 1.0 N
- 16. MOUNTING NUT TORQUE: 5-14 Nm
- 17. INGRESS PROTECTION: IP67, IK10
- 18. HARDWARE SUPPLIED: O-RING AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®	OBJECT ID
B	ECO-100302	UPDATE PANEL CUTOUT	09/27/21	JS		000026347
					TITLE	ULV7F2BSS605
					SCALE	3:2
					DATE	10/23/2019
					DR	MW
					DWG	T970068
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					REV	B