


- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
  2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
  3. TERMINAL NUMBERS FOR REF ONLY
  - ▲ 4. CONTACT MATERIAL: GOLD
  5. RATING: 3A 250 VAC cUL
  6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
  7. MECHANICAL LIFE: 500,000 CYCLES.
  8. INSULATION RESISTANCE: 1,000 M $\Omega$  @ 500VDC MIN.
  9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
  10. CONTACT RESISTANCE: 50m $\Omega$  MAX. @ 1A 12VDC
  11. OPERATING TEMP.: -20°C to 55°C
  12. ▲ DENOTES CRITICAL PARAMETER.
  - ▲ 13. LAMP VOLTAGE: 20mA 24V
  14. TRAVEL: 3.2mm
  15. ACTUATION FORCE:  $3.5 \pm 1.0$  N
  16. MOUNTING NUT TORQUE: 5-14 Nm
  17. INGRESS PROTECTION: IP67. IK10
  18. HARDWARE SUPPLIED: O-RING AND HEXNUT

PANEL CUT-OUT  
PANEL THICKNESS 1-10mm



| REV | ECO NO     | DESCRIPTION          | DATE     | BY | E-SWITCH®           |           |    |         | OBJECT ID |
|-----|------------|----------------------|----------|----|---------------------|-----------|----|---------|-----------|
| B   | ECO-100299 | UPDATE PANEL CUTOOUT | 09/23/21 | JM | TITLE ULV7F2GSSG335 |           |    |         | 000026315 |
|     |            |                      |          |    | SCALE               | DATE      | DR | DWG     | REV       |
|     |            |                      |          |    | 3:2                 | 5/31/2017 | MW | T970033 | B         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED