


FEMALE PLUG M12 STRAIGHT TO MALE PLUG M12 STRAIGHT




NOTES:

RATED VOLTAGE: 3, 4 contacts 250V per IEC 60664
5 contacts 60V per IEC 60664
5 contacts 250V per UL 2238
8 contacts 30V per IEC 60664

RATED CURRENT: 3, 4, 5 contacts 4A
8 contacts 2A

PROTECTION CLASS: IP 67
TEMPERATURE: -25°C / +85°C
CONTACTS POSITION FRONT VIEW:

	3 CONTACTS		4 CONTACTS		5 CONTACTS		8 CONTACTS	
FEMALE								
MALE								
CONNECTIONS	PIN	WIRE	PIN	WIRE	PIN	WIRE	PIN	WIRE
	1	BROWN	1	BROWN	1	BROWN	1	WHITE
	2	---	2	WHITE	2	WHITE	2	BROWN
	3	BLUE	3	BLUE	3	BLUE	3	GREEN
	4	BLACK	4	BLACK	4	BLACK	4	YELLOW
	5	---	5	---	5	GREY OR GREEN/YELLOW	5	GREY
							6	PINK
							7	BLUE
CODING REQUIRED TO IEC 61076-2-101								
							8	RED



SCALE 1:2

FOR OPTIONS SEE - NUMERICAL CODE - ON SHEET 2

11	SEE SHEET 2	ID CARRIER	PVC	TRANSPARENT
10	1	LABEL YELLOW	VINYL	---
	-	PRINTING FOR CABLES lxx	---	---
9	3 / 4 / 5 / 8	CONTACT MALE	SEE PART LIST	SELECTIVE Au OVER Ni
8	1	INSERT MALE BLACK	TPU	---
7	1	COUPLING NUT MALE	---	---
6	-	CABLE	SEE SHEET 2	---
5	-	OVERMOULDING BLACK	TPU	---
4	1	COUPLING NUT FEMALE	---	---
3	1	INSERT FEMALE BLACK	PUR	---
2	1	ORING RED	FPM	---
1	3 / 4 / 5 / 8	CONTACT FEMALE	SEE PART LIST	SELECTIVE Au OVER Ni
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
FUNCTIONAL SYMBOLS <											

ENGINEERING NO. - NUMERICAL CODE (Available parts see PART LIST table. Other parts available upon request).







OPTIONS

Overmold color:
Blank (Standard)=Black TPU
Blank=Yellow PVC for cables
A09, S19, S20, S26
Blank=Yellow TPE-E for cables
K03, K05
A=Grey / G=Black / Y=Yellow

Coupling Nut:
Blank (Standard)=Knurled Brass Ni Plated _____
1=Hexagonal Stainless steel _____
5=Knurled Derlin _____
7=Knurled Brass Ni Plated, Teflon Coated _____
Blank=7 for cables I20, I26, K03, K05, P82, S26
8=Type 316 stainless steel _____
9=Knurled / Hexagonal Brass Ni Plated SW13 _____


H= 2 pcs. of I/D Carrier PVC Transparent
(Cables lxx & P82 always with 2 pcs. of —
I/D Carrier even if no H in Engineering No.)

COUPLING NUT
FEMALE MALE




CABLE LENGTH TOLERANCES		
OVER [mm]	UP TO AND INCLUDING [mm]	TOLERANCES [mm]
0	305	+19
305	915	+45
915	1830	+56
1830	3660	+89
3660	7320	+165
7320	14640	+317
14640	30500	+610
30500	>	+2% OF FINISHED LENGTH



FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
FA = 0 FE = 0 FP = 0 DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC: CORRECTED TYPO FOR UL VALUE FROM PLC TO PLTC, FOR CABLE TYPE K03				molex CSE M12 XP AC FE STR MA STR XM DE PRODUCT CUSTOMER DRAWING					
		mm		1:1											
		GENERAL TOLERANCES (UNLESS SPECIFIED)													
		ANGULAR TOL ± 1.0°													
		4 PLACES		±											
3 PLACES		±		EC NO: 814917				2025/03/06							
2 PLACES		± 0.05		DRWN: VHANDI				2025/03/06							
1 PLACE		± 0.3		CHK'D: RSILLER				2025/03/06							
0 PLACES		± 0.5		APPR: RSILLER				2025/03/06							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
				A3-SIZE		120066		1200668165		PSD		000		A8	
								MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
								SEE PART LIST		GENERAL MARKET				2 OF 5	



PART NO.	ENGINEERING NO.	FINISHED LENGTH	POLES	CABLE DIA.
1200660675	883030K05M005	0.5M [1FT 8 IN]	3	.20[5.1]
1200660695	884030K05M100	10M [32FT 10 IN]	4	.21[5.3]
1200662239	885030K05M300	30M [98FT 5 IN]	5	.23[5.8]



- NOTES:
- 1. MATERIAL: AS NOTED
 - 2. FINISH: AS NOTED
 - 3. ELECTRICAL:
VOLTAGE: 250V
CURRENT: 4A
 - 4. TEMP RATING: -20°TO +105°C
 - 5. PROTECTION: IP67 (WHEN MATED)
 - 6. COUPLING THREAD: M12 X 1
 - 7. UL RECOGNIZED FILE: E152210
CSA CERTIFIED FILE: LR6837
 - 8. ALL DIMENSIONS ARE FOR REFERENCE
UNLESS TOLERACED OR NOTED OTHERWISE



CABLE FLEX CHARACTERISTICS

TORSIONAL FLEX TEST	5 MILLION CYCLES PER MIL-C-13777G
BEND FLEX TEST	6.5 MILLION CYCLES PER MIL-C-13777G
DRAG CHAIN TEST	20 MILLION CYCLES PER MIL-C-13777G
WELD SLAG RESISTANCE	WOODHEAD STANDARD S-300

10	WRAP LABEL	VINYL	BLACK/WHITE
9	OVERMOLD	TPC	YELLOW
8	MALE COUPLING NUT	BRASS	NICKEL PLATED
7	CONTACT PIN	COPPER ALLOY	GOLD PLATED
6	MALE INSERT	PUR	BLACK
5	O-RING	VITON	RED
4	FEMALE COUPLING NUT	BRASS	NICKEL PLATED
3	CONTACT SOCKET	COPPER ALLOY	GOLD PLATED
2	FEMALE INSERT	PUR	BLACK
1	#22/3-5 AWG CABLE	TPE JACKET	YELLOW
ITEM	DESCRIPTION	MATERIAL	FINISH

PART NUMBER LEGEND

883030K05M005

POLES: 3,4 & 5

CABLE TYPE
22AWG
TPE YELLOW

FINISHED LENGTH:
M005 = 0.5 METER
M010 = 1 METER
M100 = 10 METER

CABLE LENGTH TOLERANCES

<.3M [1FT]: +19mm-0 [+.75in-0]

.3 - .9M [1 - 3FT]: +44.5mm-0 [+1.75in-0]

.9 - 1.8M [3 - 6FT]: +55.6mm-0 [+2.19in-0]

1.8 - 3.7M [6 - 12FT]: +88.9mm-0 [+3.50in-0]

3.7 - 7.3M [12 - 24FT]: +165.1mm-0 [+6.50in-0]

7.3-14.6M [24 - 48FT]: +317.5mm-0 [+12.50in-0]

14.6 - 30.5M [48-100FT]: +622.3mm-0 [+24.50in-0]

OVER 30M [100FT] +2% OF FINISHED LENGTH

FUNCTIONAL SYMBOLS FA=0 FE=0 FP=0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	DIMENSION UNITS		SCALE		CURRENT REV DESC: ITEM-9 WAS TPE. ITEM-10 WAS BLACK/YELLOW. MODIFIED CABLE FLEX CHART, TEMP RATING AND PART NUMBER CHART			molex					
	INCH/MM		NTS										
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 785985			MICRO-CHANGE CORDSET, M12 3-5 POLE, MALE-FEMALE, STRAIGHT, SINGLE KEY, #22AWG TPE CABLE					
		mm	INCH										
	4 PLACES		± ----	± ----		DRWN: ABENJAMINLW			2024/05/07				
	3 PLACES		± ----	± ----		CHK'D: PDODDAMANEMY			2024/05/13				
	2 PLACES		± ----	± ----		APPR: BWOODMAN			2024/05/13				
	1 PLACE		± ----	± ----		INITIAL REVISION:			DOCUMENT NUMBER SD-120066-011				
	0 PLACES		± ----	± ----		DRWN: LSTEMMLE						2010/01/25	
ANGULAR TOL		±	---- °		APPR: NSTAUDIG			2010/01/29					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				C-SIZE		120066		SEE CHART		GENERAL MARKET		1 OF 1	