


FEMALE PLUG M12 STRAIGHT


NOTES:
RATED VOLTAGE: 3, 4 contacts 250V
5 contacts 60V
8 contacts 30V
RATED CURRENT: 3, 4, 5 contacts 4A
8 contacts 2A
PROTECTION CLASS: IP 67
TEMPERATURE: -25°C / +85°C



CONTACTS POSITION FRONT VIEW:

3 CONTACTS		4 CONTACTS		5 CONTACTS		8 CONTACTS	
PIN	WIRE	PIN	WIRE	PIN	WIRE	PIN	WIRE
1	BROWN	1	BROWN	1	BROWN	1	WHITE
2	---	2	WHITE	2	WHITE	2	BROWN
3	BLUE	3	BLUE	3	BLUE	3	GREEN
4	BLACK OR YELLOW/GREEN	4	BLACK	4	BLACK	4	YELLOW
5	---	5	---	5	GREY OR YELLOW/GREEN	5	GREY
						6	PINK
						7	BLUE
						8	RED
CODING REQUIRED TO IEC 61076-2-101							
DOCUMENT STATUS	P1	RELEASE DATE	2025/05/16	14:46:25			

FOR OPTIONS SEE - NUMERICAL CODE - ON SHEET 2

7	1	LABEL YELLOW	VINYL	---
	-	PRINTING FOR CABLES lxx	---	---
6	-	CABLE	SEE SHEET 2	---
5	-	OVERMOLDING BLACK	TPU	---
4	1	COUPLING NUT FEMALE	BRASS	NICKEL
3	1	INSERT FEMALE BLACK	PUR	---
2	1	ORING RED	FPM	---
1	3 / 4 / 5 / 8	CONTACT M12 FEMALE	BRASS	SELECTIVE Au OVER Ni
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
DIMENSION UNITS		CURRENT REV DESC: THE CROSS SECTION VALUE OF K03 CABLE IS UPDATED		
SCALE				
mm				
2:1				
GENERAL TOLERANCES (UNLESS SPECIFIED)		CSE M12 XP AC FE STR XM SE UNSH		
ANGULAR TOL ± 1.0 °				
4 PLACES ±		EC NO: 822303 DRWN: VHANDI 2025/05/15 CHK'D: RSILLER 2025/05/16 APPR: RSILLER 2025/05/16		
3 PLACES ±				
2 PLACES ± 0.05				
1 PLACE ± 0.3		INITIAL REVISION: DRWN: JMARSZALEK 2016/01/12 APPR: RSILLER 2016/04/08		
0 PLACES ± 0.5				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DOCUMENT NUMBER 1200658605		
THIRD ANGLE PROJECTION		DOC TYPE PSD		
		DOC PART 000		
DRAWING A3-SIZE		REVISION A8		
SERIES 120065		PRODUCT CUSTOMER DRAWING		
MATERIAL NUMBER SEE PART LIST		DOCUMENT NUMBER 1200658605		
CUSTOMER GENERAL MARKET		DOC TYPE PSD		
SHEET NUMBER 1 OF 4		DOC PART 000		

ENGINEERING NO. - NUMERICAL CODE (Available parts see PART LIST table. Others on request).

80X000XXXXXX

80=M12x1
Single ended

Contacts:
3=3 Contacts
4=4 Contacts
5=5 Contacts
8=8 Contacts

Heads style:
000=Plug Female Straight

Cable type: See Table


Units:
M=Meter
C=Centimeter

Length
Examples:
005=0.5 unit
010=1 unit
100=10 units

OPTIONS


H= 2 pcs. of I/D Carrier
PVC Transparent
(Cables lxx & P82 always
with 2 pcs. of I/D Carrier
even if no H in
Engineering No.)

COUPLING NUTS



CABLE INFORMATION (for more information see Cable Data Sheet).

CABLE TYPE	NO. OF WIRES	CROSS SECTION	CABLE JACKET	UL	CSA	STATIC: TEMP. / BENDING RADIUS	DYNAMIC: TEMP. / BENDING RADIUS	DRAG CHAIN	SHIELD
E13	3	18AWG	PVC YELLOW	UL 2661/1731	I/II A/B 80°C/300V	-	-	-	-
E52	3 / 4 / 8	0.34mm²	PVC GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	-
E63	5	0.34mm²	PVC GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	YES
H12	4	0.50mm²	PUR BLACK LS0H	UL 21198/10493	C22.2 I/II A/B 80°C/300V	-50°C to +80°C, 5xO.D.	-25°C to +80°C, 10xO.D.	2 000 000, Temp max 60°C	-
H69	4	0.20mm²	PUR GREY LS0H	-	-	-	-	-	-
I02	3 / 4 / 8	0.25mm²	PVC CEI GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	-
I03	3 / 4 / 5	0.34mm²	PVC CEI GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	-
I04	4	0.50mm²	PVC CEI GREY	-	-	-25°C to +70°C	-5°C to +70°C	-	-
I20	3 / 4	0.34mm²	PVC CEI GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	YES
I26	5	0.34mm²	PVC CEI GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	-
K03	4 / 5	0.75mm²	TPE YELLOW	UL JEC 60332-1 or PLCT	I/II 90°C/300V	-	-	-	-
K05	3 / 4 / 5	0.34mm²	TPE YELLOW	UL ITC E195601 or PLC	I/II A/B 90°C/300V	-	-	-	-
P04	4	0.50mm²	PUR BLACK	-	-	-40°C to +90°C, 7.5xO.D.	-15°C to +90°C, 12.5xO.D.	-	-
P12	3 / 5	0.50mm²	PUR BLACK	-	-	-30°C to +90°C	-5°C to +90°C	-	-
P19	8	0.25mm²	PUR BLACK	-	-	-40°C to +90°C, 7.5xO.D.	-15°C to +90°C, 12.5xO.D.	2 000 000 cycles, 15xO.D.	YES
P20	3 / 4 / 5	0.34mm²	PUR BLACK LS0H	-	-	-30°C to +80°C	-	-	YES
P82	3 / 4 / 5	0.34mm²	PUR IRR ORANGE	-	-	-50°C to +105°C, 5xO.D.	-40°C to +105°C, 7.5xO.D.	-	-
S19	8	0.25mm²	PVC YELLOW	UL 2661/1569	C22.2 II A 105°C/300V	-30°C to +105°C, 10xO.D.	-15°C to +105°C, 15xO.D.	-	YES
S20	3 / 4 / 5	0.34mm²	PVC YELLOW	UL 2661/1731	C22.2 II A 105°C/300V	-30°C to +105°C	-	-	YES
S26	5	0.34mm²	PVC YELLOW	UL 2661/1731	C22.2 II A 105°C/300V	-30°C to +105°C	-	-	YES



SCALE 1:1

CABLE LENGTH TOLERANCES

OVER	UP TO AND INCLUDING	TOLERANCES
0	305mm	+19mm
305mm	915mm	+45mm
915mm	1830mm	+56mm
1830mm	3660mm	+89mm
3660mm	7320mm	+165mm
7320mm	14640mm	+317mm
14640mm	30500mm	+610mm
30500mm	>	+2% of finished length

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 1.0 °

4 PLACES ±

3 PLACES ±

2 PLACES ± 0.05

1 PLACE ± 0.3

0 PLACES ± 0.5

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: THE CROSS SECTION VALUE OF K03 CABLE IS UPDATED

EC NO: 822303
DRWN: VHANDI
CHK'D: RSILLER
APPR: RSILLER

2025/05/15
2025/05/16
2025/05/16

INITIAL REVISION:
DRWN: JMARSZALEK
APPR: RSILLER

2016/01/12
2016/04/08

THIRD ANGLE PROJECTION

DRAWING

SERIES

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER

moLEX

CSE M12 XP AC FE STR XM SE UNSH

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

1200658605

DOC TYPE

PSD

DOC PART

000

REVISION

A8

SEE PART LIST

GENERAL MARKET

2 OF 4

DOCUMENT STATUS P1 RELEASE DATE 2025/05/16 14:46:25

987654321

10	9	8	7	6	5	4	3	2	1
PART LIST									
MOLEX P/N			ENGINEERING No.		L [mm]				
3P CABLE E13									
1200658524			803000E13M030		3000				
3P CABLE E52									
1200651767			803000E52M050A		5000				
1200658293			803000E52M3001A		30000				
4P CABLE E52									
1200064254			804000E52M010A		1000				
1200651778			804000E52M050A		5000				
1200651857			804000E52M100A		10000				
1200060436			804000E52M200A		20000				
1200061620			804000E52M3001A		30000				
1200063819			804000E52K0011A		100000				
8P CABLE E52									
1200657335			808000E52M005		500				
1200658236			808000E52M020		2000				
1200062049			808000E52M050		5000				
1200659997			808000E52M100		10000				
5P CABLE E63									
1200658015			805000E63M020A		2000				
1200061936			805000E63M050A		5000				
4P CABLE H12									
1200659593			804000H12M020		2000				
1200659767			804000H12M0209		2000				
1200659768			804000H12M0309		3000				
1200659113			804000H12M050		5000				
1200659769			804000H12M0509		5000				
1200659271			804000H12M100		10000				
1200659770			804000H12M1009		10000				
3P CABLE H69									
1200062094			803000H69M050		5000				
4P CABLE H69									
1200061680			804000H69M050		5000				
1200658242			804000H69M300		30000				
8P CABLE I02									
1200658677			808000I02M010		1000				
1200658678			808000I02M020		2000				
1200658679			808000I02M030		3000				
1200658680			808000I02M040		4000				
1200658681			808000I02M050		5000				
1200658682			808000I02M100		10000				

NOTES:

✱ - Part No. with Yellow PVC overmolding

DOCUMENT STATUS	P1	RELEASE DATE	2025/05/16	14:46:25					
10	9	8	7	6	5	4	3	2	1

