




M12 X-CODE
MALE
FRONT VIEW





ARROW IN LINE WITH THE CODING
BRAD LOGO ON OTHER SIDE

M12 X-CODE
MALE
FRONT VIEW



M12 X-CODE
MALE
FRONT VIEW



SCALE 1:2

NOTES:

VOLTAGE RATING: 48 V

CURRENT RATING: 0.5 A

TEMPERATURE RATING:

STATIC: -40 °C TO 80 °C

DYNAMIC: -20 °C TO 80 °C

IP RATING: IP 67 (IN MATED AND LOCKED CONDITION)

TRANSMISSION CHARACTERISTICS ACCORDING TO ISO/IEC 11801 CLASS EA CHANNEL,
WITH INSERTION LOSS BEING IGNORED FOR CABLE LENGTHS ≤ 1 m OR ≥ 65 m

POWER TRANSMISSION TEST ACCORDING IEEE802.3bt UP TO 65m LENGTH

PACKAGING: CORDSETS ARE PACKED IN A POLYBAG

BILL OF MATERIAL

ITEM	QTY	DESCRIPTION	MATERIAL	FINISH/COLOR
1	1	CABLE	TPE	TEAL
2	16	CONTACT 6 MALE	BRASS	Au OVER Ni
3	-	MOLDING MATERIAL	TPU	BLACK
4	2	INSERT M12 CAT6A MALE 8P	PA6	BLACK
5	2	SHELL M12 CAT6A	ZINC DIE-CAST	Ni PLATED
6	2	NUT M12 MALE	BRASS	Ni PLATED
7	1	LABEL 2.0X1.75	VINYL	YELLOW

DOCUMENT STATUS	P1	RELEASE DATE	2024/05/15	09:03:53
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	CURRENT REV DESC:	molex			
$\nabla_A = 0$	DIMENSION UNITS	SCALE	CSE M12 CAT6A 8P XC MA STR PUR XM DE			
$\nabla_E = 1$	mm	2:1	PRODUCT CUSTOMER DRAWING			
$\nabla_F = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)	EC NO: 786254	DOCUMENT NUMBER			
DIVISIONAL SYMBOLS	ANGULAR TOL $\pm 1.0^\circ$	DRWN: MBLOESER	DOC TYPE			
	4 PLACES $\pm$	CHK'D: RSILLER	DOC PART			
	3 PLACES $\pm$	APPR: RSILLER	REVISION			
	2 PLACES ± 0.05	INITIAL REVISION:	1203411127			
	1 PLACE ± 0.3	DRWN: MBLOESER	PSD			
	0 PLACES ± 0.5	APPR: RSILLER	000			
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	A4			
		DRAWING	SHEET NUMBER			
		A3-SIZE	120341			
		SERIES	SEE TABLE 1			
		MATERIAL NUMBER	GENERAL MARKET			
		CUSTOMER	1 OF 2			

