



NOTE:  
1. ALL DIMENSIONS IN MM [INCH]  
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$   
3. TERMINAL NUMBERS FOR REF ONLY

- ▲ 4. CONTACT MATERIAL: SILVER  
5. RATING: 3A 250 VAC cUL  
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES  
AT FULL LOAD.  
7. MECHANICAL LIFE: 1,000,000 CYCLES.  
8. INSULATION RESISTANCE: 1,000 M $\Omega$  @ 500VDC MIN.  
9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE  
10. CONTACT RESISTANCE: 50m $\Omega$  MAX. @ 1A 12VDC  
11. OPERATING TEMP.: -20°C to 55°C  
12. ▲ DENOTES CRITICAL PARAMETER.  
▲ 13. LAMP VOLTAGE: 20mA 24V  
14. TRAVEL: 3.2mm  
15. ACTUATION FORCE: 2.5  $\pm$  1.0 N  
16. MOUNTING NUT TORQUE: 5-14 Nm  
17. INGRESS PROTECTION: IP67  
18. HARDWARE SUPPLIED: O-RING AND HEXNUT

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®			OBJECT ID
B	ECO-100289	UPDATE PANEL CUTOUT	09/13/21	JS				000026442
					TITLE ULV8F2B11315			
			SCALE 1:1	DATE 2/20/2019	DR MW	DWG T980054	REV B	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED								