









BOM

ITEM	DESCRIPTION
1	SCREW
2	COVER ASSEMBLY
3	INSERT ASSEMBLY
4	GASKET

C19207N21**

SERIES
C19= INTERNAL THREAD FORM C MICRO
POLES
2= 2 POLE, 3= 3 POLE
THREAD SIZE
07= PG7, M2= M12x1.5
HOUSING MATERIAL AND COLOR
G= PA6 GRAY, N= PA6 BLACK, W= PA6 BLACK V0, T= TRANSPARENT
GROUND POSITION
0= UNMOUNTED, 2= H12, 3= H3, 6= H6, 9= H9
SCREW AND GASKET
1= NBR PROFILE GASKET & SCREW
2= NBR FLAT GASKET & SCREW
3= WHITE SILICONE PROFILED GASKET & SCREW
4= WHITE SILICONE FLAT GASKET & SCREW
6= NBR FLAT GASKET, WITHOUT SCREW
A= NBR PROFILE GASKET & SCREW +2mm
B= NBR FLAT GASKET & SCREW +2mm
C= WHITE SILICONE PROFILED GASKET & SCREW +2mm
D= WHITE SILICONE FLAT GASKET & SCREW +2mm

NON STANDARD COMPONENTS
14= SINGLE PACKED IN NEUTRAL BAG
5N= SINGLE PACKED
6X= WITHOUT RING NUT OR CABLE FIXING NUT
P7= IP67 COMPLIANT
S6= CUSTOM SCREW M3x26
SA= UL LISTED
0217=3 BAGS OF 100PCS PER CARTON



- NOTES:
- PLEASE SEE SHEET 2 FOR CURRENTLY CONFIGURED PART NUMBERS
FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES OR CONSULT
THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED
 - EARTH POSITION SHOWN. H12
 - FOR PACKAGING SEE PACKAGING SPEC PK-121023-C19
 - PRODUCT SPEC: SEE PS-121201-001
 - PART NO. 1210230465 SHOWN FOR ILLUSTRATION PURPOSE ONLY

LAST INSPECTION NO. 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
FUNCTIONAL SYMBOLS	DIMENSION UNITS		SCALE	CURRENT REV DESC: NEW OPTION S6 AVAILABLE					molex INTERNAL THREAD C19 SERIES				

molex

INTERNAL THREAD
C19 SERIES

PRODUCT CUSTOMER DRAWING

SD-121023-005

PSD 001 C1

DOCUMENT STATUS	P1	RELEASE DATE	2024/10/01	09:25:18
-----------------	----	--------------	------------	----------

