


10	9	8	7	6	5	4	3	2	1
MAT'L NO.	ENG. NO.	STUD SIZE	"S" ±.010 (0.25)	"W" MAX	"L" REF	"T" REF			
191640889	SD-656-08	#8	.173 (4.39)	.38 (9.7)	1.46 (37.1)	.045 (1.14)			
191640080	SD-656-10	#10	.198 (5.03)						
191640081	SD-651-14	1/4	.265 (6.73)	.60 (15.2)	1.67 (42.4)				
191640083	SD-651-56	5/16	.328 (8.33)						



NOTE(S):

1 TERMINAL MATERIAL: COPPER ALLOY

FINISH: ELECTRO-TIN PLATE

2 INSUL. MATERIAL: HEAT SHRINKABLE TUBING WITH HOTMELT
ADHESIVE INNER LINER

COLOR: RED

3 MWID = MAXIMUM WIRE INSULATION DIAMETER.

4. ASSEMBLY IS RoHS COMPLIANT.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#514354		molex			
DIMENSION UNITS INCH/MM		SCALE NTS					
GENERAL TOLERANCES (UNLESS SPECIFIED)							
		MM	INCH				
4 PLACES	±	±		EC NO: 804939			
3 PLACES	±	±		DRWN: MADHAM5	2024/11/14		
2 PLACES	±	±		CHK'D: GGA	2024/12/10		
1 PLACE	±	±		APPR: GGA	2024/12/10		
0 PLACES	±	±					
ANGULAR TOL: ± °				INITIAL REVISION:			
				DRWN: DBUNNELL	2000/09/06		
				APPR: RDEROSS	2000/09/13		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION			
				DRAWING			
				SERIES			
DOCUMENT STATUS		SEE CHART	CUSTOMER	SHEET NUMBER			
P1		GENERAL MARKET	1 OF 1				
RELEASE DATE		2024/12/10	06:45:28				