

9		8		7	6		5		4	3	2	1
MAT'L NO (LOOSE PC)	ENG NO (LOOSE PC)	MAT'L NO (ON TAPE)	ENG NO (ON TAPE)	STUD SIZE	Ø"S"	Ø"W" MAX	"A" MIN	"L" MAX	1.070 REF [27.18] PARTS ON TAPE 1.070 REF [27.18] OPTIONAL DOUBLE SPACED 191930156 (D-350-14TD)			
191930143	D-350-06	-	-	6	.146 (3.71)	.483 (12.27)	.368 (9.35)	.977 (24.82)				
191930146	D-350-08	191930148	D-350-08T	8	.173 (4.39)							
191930149	D-350-10	191930151	D-350-10T	10	.198 (5.03)							
191930152	D-350-14	191930155	D-350-14T	1¼	.265 (6.73)							
191930157	D-350-56	191930158	D-350-56T	5⁄16	.328 (8.33)							
191930159	D-351-10	-	-	10	.198 (5.03)	.603 (15.32)	.433 (11.00)	1.102 (27.99)				
191930163	D-351-14	191930166	D-351-14T	1¼	.265 (6.73)							
191930171	D-351-56	191930174	D-351-56T	5⁄16	.328 (8.33)							
191930167	D-351-38	191930170	D-351-38T	3⁄8	.390 (9.91)							
191930175	D-351-76	-	-	7⁄16	.453 (11.51)							
191930194	D-353-56	-	-	5⁄16	.328 (8.33)	1.140 (28.96)	.993 (25.22)	1.938 (49.23)				
191930193	D-353-38	-	-	3⁄8	.390 (9.91)							
191930196	D-353-76	-	-	7⁄16	.453 (11.51)							
191930190	D-353-12	-	-	1⁄2	.515 (13.08)							
191930195	D-353-58	-	-	5⁄8	.656 (16.66)							
191930192	D-353-34	-	-	3⁄4	.781 (19.84)							
191930198	D-356-06	191930199	D-356-06T	6	.146 (3.71)	.389 (9.88)	.368 (9.35)	.930 (23.62)				
191930200	D-356-08	191930201	D-356-08T	8	.173 (4.39)							
191930202	D-356-10	191930203	D-356-10T	10	.198 (5.03)							
191930204	D-356-14	191930205	D-356-14T	1¼	.265 (6.73)							

NOTES:

1. MATERIAL: TIN PLATED COPPER.

2. MUST BE RoHS COMPLIANT.

Ø .165 MIN
[4.19]

.315 MIN
[8.00]

"A" MIN

"L" MAX

Ø"S"

Ø"W"

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE		CURRENT REV DESC: ADDED D-351, D-353, AND D-356 PN'S				molex				
IN/MM		NTS										
GENERAL TOLERANCES (UNLESS SPECIFIED)												
	MM	INCH										
4 PLACES	±		±	EC NO: 821384				RING TONGUE TERMINAL 8 AWG, BRAZED SEAM				
3 PLACES	±		± 0.005	DRWN: DEANNM1 2025/05/06								
2 PLACES	±	0.13	± 0.01	CHK'D: ETHRODAHL 2025/05/08								
1 PLACE	±	0.25	±	APPR: ETHRODAHL 2025/05/08								
0 PLACES	±		±	INITIAL REVISION:				DOCUMENT NUMBER				
ANGULAR TOL ± 0.5 °				APPR: HEB 2001/01/23				SD-19193-016				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER		
						B-SIZE	19193	SEE CHART	GENERAL MARKET	1 OF 1		
DOCUMENT STATUS		P1	RELEASE DATE	2025/05/08	16:33:49							
9		8		7	6	5	4	3	2	1		

FORMAT: Eng-lega-master-ib-prod-B
REVISION: D
DATE: 2018/01/18