


▲





O.P. (MM)	F.P. (MM)
6.5 ± 0.3	7.5 MAX

O.P. = OPERATING POINT
F.P. = FREE-POSITION



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- RATING: 0.1A @ 125VAC; 2A @ 12VDC;
0.5A @ 42VDC; 1A @ 24VDC;
UL, CUL APPROVED
- OPERATING FORCE: 70 ± 30 GRAMS.
- OPERATING TEMP: -25°C to 85°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- MECHANICAL LIFE: 1,000,000 CYCLES TYP.
- INSULATION RESISTANCE: >100 MEGA-OHMS @ 500VDC
- DIELECTRIC STRENGTH: 600VAC
- CONTACT RESISTANCE: 100 MILLI-OHMS MAX (INITIAL).
- WIRES ARE 22AWG, STRANDED, UL1007, COLOR AS NOTED
- 2011/65/EU (ROHS) COMPLIANT.
- ▲ DENOTES CRITICAL PARAMETER.
- ACTUATION BELOW THE 5.6mm ACTUATION LIMIT MAY CAUSE DAMAGE TO THE INTERNAL CONTACTS.



C	23894	correct note 4 to 70 grams	5/14/19	MW
B	22783	Updated wire cover	3/28/17	rc
A	22608	New Release	11/30/16	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE WS0850100F070WA

SCALE

2:1

DATE

8/17/2016

DR

rc

DWG

Q930006

REV

C