





REF. -50 OPT. SCREW
(WHERE APPLICABLE)



3 CIRCUIT SHOWN
FOR REFERENCE




NOTES:

1. MATERIAL: SEE TABLE.
2. FINISHES: SEE TABLE.
3. PRODUCT SPECIFICATION: NOT REQUIRED.
4. "XX" REFERS TO THE QUANTITY OF CIRCUITS.
5. ROHS COMPLIANT.

4	XX	SCRW&WSHR,#6-32X.25 PANHD,PH-SL (OPT -50)	STEEL	ZN, CLEAR CHROMATE
4	XX	SCREW #6-32X.250 BHD PHSL (OPT -49)	BRASS	NICKEL PLATE
3	XX	SCREW #6-32X.250 BHD PHSL (STD)	STEEL	ZN, CLEAR CHROMATE
2	XX	TERM WW 6C SN-KT	BRASS	TIN PLATE
1	1	INSULATOR SR BTS PC MOMTG	POLYESTER (PBT)	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

DOCUMENT STATUS	P1	RELEASE DATE	2024/12/10	06:45:29
-----------------	----	--------------	------------	----------

NO OF CIRCUITS	DIM "A"		DIM "B"		ASSY. MAT. NO. (STD -C)	ASSY. MAT. NO. (-C -49 OPT)	ASSY. MAT. NO. (-C -50 OPT)
	mm	Inch	mm	Inch			
2	21.1	0.83	9.53	0.375	-----	387212902	387213502
3	30.6	1.21	19.05	0.750	-----	-----	-----
4	40.2	1.58	28.58	1.125	387212304	387212904	387213504
5	49.7	1.96	38.10	1.500	-----	-----	-----
6	59.2	2.33	47.63	1.875	-----	387212906	387213506
7	68.7	2.71	57.15	2.250	387212307	387212907	-----
8	78.3	3.08	66.68	2.625	387212308	387212908	-----
9	87.8	3.46	76.20	3.000	-----	387212909	-----
10	97.3	3.83	85.73	3.375	-----	387212910	-----
11	106.8	4.21	95.25	3.750	-----	387212911	387213511
12	116.4	4.58	104.78	4.125	-----	387212912	-----
13	125.9	4.96	114.30	4.500	-----	387212913	-----
14	135.4	5.33	123.83	4.875	387212314	387212914	387213514
15	144.9	5.71	133.35	5.250	387212315	387212915	387213515
16	154.5	6.08	142.88	5.625	-----	387212916	387213516
17	164.0	6.46	152.40	6.000	387212317	387212917	387213517
18	173.5	6.83	161.93	6.375	-----	387212918	-----
19	183.0	7.21	171.45	6.750	387212319	387212919	387213519
20	192.6	7.58	180.98	7.125	-----	387212920	-----
21	202.1	7.96	190.50	7.500	387212321	387212921	387213521
22	211.6	8.33	200.03	7.875	387212322	387212922	387213522
23	221.1	8.71	209.55	8.250	387212323	387212923	387213523
24	230.7	9.08	219.08	8.625	-----	387212924	387213524
25	240.2	9.46	228.60	9.000	387212325	387212925	-----
26	249.7	9.83	238.13	9.375	387212326	387212926	387213526

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#514354			molex			
mm/IN		2:1								
GENERAL TOLERANCES (UNLESS SPECIFIED)							9.53MM/.375" PCB BARRIER TERMINAL STRIP NO MOUNTING ENDS			
	MM		INCH							
4 PLACES	±		±							
3 PLACES	±		± 0.005							
2 PLACES	±	0.13	± 0.01		PRODUCT CUSTOMER DRAWING					
1 PLACE	±	0.3	±							
0 PLACES	±		±							
ANGULAR TOL ± 2.0°				DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION	
				SD-38721-006			PSD	001	A2	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
						B-SIZE	38721	SEE TABLE	GENERAL MARKET	1 OF 1