




NOTES:

- MATERIALS:
CONTACT: BERYLLIUM COPPER
FERRULE: BRASS
INSULATOR: PEEK
ALL OTHER METAL PARTS: STAINLESS STEEL
- FINISH:
CONTACT & FERRULE: GOLD
ALL OTHER METAL PARTS: PASSIVATED
- ELECTRICAL:
IMPEDANCE: 50Ω
FREQUENCY RANGE: DC TO 40GHz
VSWR: 1.30 MAX

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: UPDATED TOLERANCE BLOCK					molex 2.92mm FEMALE BULKHEAD FOR .047 CABLE EWR16564-A				
	MM/INCH		NTS											
	GENERAL TOLERANCES (UNLESS SPECIFIED)													
			MM	INCH	STATUS: Production DRWN: James Borrelli 2024-10-07 CHK'D: Alex Robertson 2024-10-10 APPR: Kevin Tagan 2024-10-10					PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER732520290DOC TYPEPSDDOC PART000REVISIONA2				
	4 PLACES	±		±										
	3 PLACES	±	0.1000	±										
	2 PLACES	±	0.200	±										
1 PLACE	±	0.30	±											
0 PLACES	±		±	FIRST ANGLE PROJECTIONDRAWINGC-SIZESERIES73252MATERIAL NUMBER0732520290CUSTOMERSHEET NUMBER1 OF 1										
ANGULAR TOL		±	5°											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS														

2.92mm FEMALE BULKHEAD FOR .047 CABLE
EWR16564-A

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
732520290	PSD	000	A2