


SERPAC 1924AA

ELECTRONIC ENCLOSURES



PART NO.	DESCRIPTION (Included)	PART NO.	DESCRIPTION
9-2	Top	50	Non-Skid Feet
194AA	4AA Bottom	60	Standoff Hole
6005	#4X3/8" Self-Tapping Screw (8)	61	Standoff Post
1026	Access Door	SK9	Waterproof Seal Kit
73	Double Battery Contact (3)		
72	Single Battery Contact (2)		

Notes: Enclosure weight .70 lb / 319 g

1) Enclosure meets or exceeds IP40 and NEMA 1

2) Circuit Board drawings see sheet 3.





3) All components are RoHS Compliant.

4) Material: Top and Bottom ABS.


5) When used with SK9 the enclosure meets or exceeds IP 67 and NEMA 4X, 12 and 13 MIL-STD-810G 506.5 (.04 lb / 19g)

SERPAC 1924AA

ELECTRONIC ENCLOSURES




- Notes:
- 1) Enclosure meets or exceeds IP40 and NEMA 1
 - 2) Circuit Board drawings see sheet 3.
 - 3) All components are RoHS Compliant.
 - 4) Material: Top and Bottom ABS.
 - 5) Customizable molding areas. $\triangle 5$
 - 6) PCB Bosses accept #4 self tapping screw. $\triangle 6$
 - 7) When used with SK9 the enclosure meets or exceeds IP 67 and NEMA 4X, 12 and 13 MIL-STD-810G 506.5 (.04 lb / 19g)




SERPAC 1924AA CIRCUIT BOARD

ELECTRONIC ENCLOSURES

Top Option



Bottom Option A



Bottom Option B

