

## SPECIFICATIONS:

## MATERIALS:

HOUSING: PBT, UL94 V-0, BLACK  
 CONTACTS: 10 $\mu$ " GOLD PLATED BRASS  
 NUT: NICKEL PLATED BRASS  
 SHELL: NICKEL PLATED BRASS  
 ORING: EPDM, BLACK





## ELECTRICAL:

RATED CURRENT: 1.5A  
 RATED VOLTAGE: 30V  
 INSULATION RESISTANCE: 100 M $\Omega$ MS MIN.  
 CONTACT RESISTANCE: 10 m $\Omega$ MS MAX.

## ENVIRONMENT:

OPERATING TEMPERATURE: -40°C TO +85°C  
 WATER PROOF: IP67

MAX WIRE AWG: 26 AWG



NUT

RECOMMENDED PANEL CUT-OUT

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE  
 THE PROPERTY OF NorComp AND SHALL NOT  
 BE REPRODUCED, COPIED OR USED AS THE  
 BASIS FOR THE MANUFACTURE OR SALE OF  
 APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
J. KADELDATE:  
12/11/2023

NorComp

SCALE:	NTS	SHEET	OF	REV
DWG NO.	859-017-203R004	1	1	0