

BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (2) 4-40 JACKSCREWS
- (2) HOUSING SCREWS
- (4) STRAIN RELIEF SCREWS
- (2) STRAIN RELIEF CLAMP
- (1) COVER PLATE




SPECIFICATIONS:

MATERIALS:

| | |
|-----------------------|---------------------|
| BACKSHELL: | DIE-CAST ZINC ALLOY |
| BACKSHELL PLATING: | NICKEL OVER COPPER |
| JACKSCREWS: | ZINC PLATED STEEL |
| HOUSING SCREWS: | ZINC PLATED STEEL |
| STRAIN RELIEF SCREWS: | ZINC PLATED STEEL |
| COVER PLATE: | ZINC PLATED STEEL |
| STRAIN RELIEF CLAMP: | ZINC PLATED STEEL |

ENVIRONMENT:

OPERATING TEMPERATURE: -40°C TO +120°C



RECOMMENDED CABLE DIAMETER: 0.189 [4.80] - 0.433 [11.00]

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

05/12/2015

GENERAL TOLERANCE
ANGLE ($±5^\circ$)
LINEAR = $±0.015$ [$±0.38$]

UNITS = inch [mm]

NorComp

| SCALE: | NTS | 1 | 1 | REV 3 |
|---------|-----------------|---|---|----------|
| DWG NO. | 959-025-030R121 | | | |