

1. CONNECTOR 1 : 858-008-203RLS4, MOLDED RIGHT ANGLE HOOD, COLOR BLACK
2. WIRE : 24AWG, 4 TWISTED PAIRS, UL2835, FOIL SHIELD, COLOR BLACK, 30V
3. CABLE DIAMETER : 0.256 [6.50]  $\pm 0.007$  [ $\pm 0.19$ ]
4. PIN OUT :

### WIRING SCHEMATIC

Pin #1		BROWN	
Pin #2		BROWN/WHITE	
Pin #3		BLUE	
Pin #4		BLUE/WHITE	
Pin #5		ORANGE	
Pin #6		ORANGE/WHITE	
Pin #7		GREEN	
Pin #8		GREEN/WHITE	
DRAIN		SHIELD	

CCA-000-MYYR217

- 01 = 1 METER
- 02 = 2 METERS
- 03 = 3 METERS

\*\*SEE PAGE 3 FOR CABLE  
SPECIFICATIONS

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.



DRAWN:  
M. SIGMON  
DATE:  
04/15/2015

NorComp

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

SCALE: NTS	SHEET 1 OF 3	REV 4
DWG NO.	CCA-000-MYYR217	



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
M. SIGMON  
DATE:  
04/15/2015

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 2	OF 3	REV 4
DWG NO. CCA-000-MYYR217			

## ELECTRICAL CHARACTERISTICS

VOLTAGE RATING : 30V



TEMPERATURE RATING : 60°C

SPARK TEST : AC-2000V/0.15 sec MIN.

DIELECTRIC STRENGTH : AC-750V/1 sec MIN.

INSULATION RESISTANCE : PE: DC-500V 15000 MΩHM/100M MIN. AT 20°C

CONDUCTOR RESISTANCE : 24AWG - 93.2 ΩHM/KM MAX. AT 20°C



## COLOR CODE

1. BROWN \* BROWN/WHITE
2. BLUE \* BLUE/WHITE
3. ORANGE \* ORANGE/WHITE
4. GREEN \* GREEN/WHITE

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
M. SIGMONDATE:  
04/15/2015

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 3	OF 3	REV 4
---------------	------------	---------	----------

DWG NO.

CCA-000-MYYR217