



599 SERIES

Infrared SMD LED

1206 Package Top View 940nm

MECHANICAL / SPECIFICATIONS

PART NUMBER:
[599-12C0-147IRF](#)

DIMENSIONS:
3.2 x 1.6 x 1.1mm

LENS COLOR:
Clear

LENS MATERIAL:
Epoxy

STANDARD PACKAGING:
3000/reel


MOISTURE SENSITIVITY LEVEL:
2a

CERTIFICATIONS & RATINGS


RoHS Compliant

DIMENSIONS inches [mm]


TOP VIEW




SIDE VIEW



BOTTOM VIEW



RECOMMENDED PAD LAYOUT



LED SCHEMATIC



ABSOLUTE MAXIMUM RATINGS AT 25°C

Symbol	Parameter	Ratings	Units	Notes
I_F	Forward Current	65	mA	
I_{FP}	Peak Current	250	mA	1
V_R	Reverse Voltage	5	V	
T_{opr}	Operating Temperature	-40~+85	°C	
T_{stg}	Storage Temperature	-40~+100	°C	
T_{sol}	Soldering Temperature	260	°C	2
P_d	Total Power Dissipation	110	mW	


Notes:

- IFP Conditions — Pulse Width ≤ 100μs and Duty ≤ 1%.
- Soldering time ≤ 5 seconds.


ELECTRICAL - OPTICAL CHARACTERISTICS

Symbol	Parameters	Test Conditions	Min	Typ	Max	Unit
I_e	Radiant Intensity	$I_F=20mA$	0.5	0.85	2.0	mW/sr
λ_p	Peak Wavelength	$I_F=20mA$	-	940	-	nm
$\Delta\lambda$	Spectral bandwidth	$I_F=20mA$	-	50	-	nm
V_F	Forward Voltage	$I_F=20mA$	1.2	-	1.8	V
I_R	Reverse Current	$V_R=5V$	-	-	10	μA
$2\theta_{\frac{1}{2}}$	Angle of Half Intensity	$I_F=20mA$	-	140	-	deg


TYPICAL ELECTRICAL-OPTICAL CHARACTERISTICS



TAPE AND REEL SPECIFICATION



Dim A	Dim B	Dim C	Quantity/Reel
3.50±0.10	1.88±0.10	1.27±0.10	3K



Unit: mm

REFLOW SOLDERING

Recommended soldering paste specifications:

1. Operating temp.: Above 220°C, 60sec.
2. Peak temp.: 260°C Max., 10sec Max.
3. Reflow soldering should not be done more than two times.

LEAD-FREE SOLDER PROFILE

