


FEMALE PLUG M12 STRAIGHT TO MALE PLUG M12 STRAIGHT



NOTES:

RATED VOLTAGE: 3, 4 contacts 250V per IEC 60664
5 contacts 60V per IEC 60664
5 contacts 250V per UL 2238
8 contacts 30V per IEC 60664

RATED CURRENT: 3, 4, 5 contacts 4A
8 contacts 2A

PROTECTION CLASS: IP 67
TEMPERATURE: -25°C / +85°C

CONTACTS POSITION FRONT VIEW:

	3 CONTACTS		4 CONTACTS		5 CONTACTS		8 CONTACTS	
FEMALE								
MALE								
CONNECTIONS	PIN	WIRE	PIN	WIRE	PIN	WIRE	PIN	WIRE
	1	BROWN	1	BROWN	1	BROWN	1	WHITE
	2	-	2	WHITE	2	WHITE	2	BROWN
	3	BLUE	3	BLUE	3	BLUE	3	GREEN
	4	BLACK	4	BLACK	4	BLACK	4	YELLOW
					5	GREY	5	GREY
							6	PINK
							7	BLUE
CODING REQUIRED TO IEC 61076-2-101								

FOR OPTIONS SEE - NUMERICAL CODE - ON SHEET 2

11	SEE SHEET 2	ID CARRIER	PVC	TRANSPARENT
10	1	LABEL YELLOW	VINYL	-
9	3 / 4 / 5 / 8	CONTACT MALE	SEE PART LIST	SELECTIVE GOLD OVER NICKEL
8	1	INSERT MALE BLACK	TPU	-
7	1	COUPLING NUT MALE	-	-
6	-	CABLE	SEE SHEET 2	-
5	-	OVERMOULDING BLACK	TPU	-
4	1	COUPLING NUT FEMALE	-	-
3	1	INSERT FEMALE BLACK	PUR	-
2	1	O-RING RED	FPM	-
1	3 / 4 / 5 / 8	CONTACT FEMALE	SEE PART LIST	SELECTIVE GOLD OVER NICKEL
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

FUNCTIONAL SYMBOLS THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION CURRENT REV DESC: NEW P/N'S ADDED TO THE DRAWING 12335	DIVISIONAL SYMBOLS THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION CURRENT REV DESC: NEW P/N'S ADDED TO THE DRAWING 12335	SCALE 1:1	molex CSE M12 XP AC FE STR MA STR XM DE			
	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 1.0° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.05 1 PLACE ± 0.3 0 PLACES ± 0.5 DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	EC NO: 769491 DRWN: VHANDI CHK'D: RSILLER APPR: RSILLER INITIAL REVISION: DRWN: JMARSZALEK APPR: RSILLER	2023/10/30 2023/11/21 2023/11/21 2016/09/16 2016/12/08	PRODUCT CUSTOMER DRAWING		
				DOCUMENT NUMBER 1200668084		
				DOC TYPE PSD	DOC PART 000	REVISION A17
				MATERIAL NUMBER SEE SHEET 3-4	CUSTOMER GENERAL MARKET	SHEET NUMBER 1 OF 4

10	9	8	7	6	5	4	3	2	1
PART LIST									
MOLEX PN			Engineering No.			Length			
1200668174			884030H09M030			3m			
1200668380			884030H09M040			4m			
1200668244			884030H09M050			5m			
1200668550			884030H09M050H			5m			
1200668737			884030H09M055			5.5m			
1200669926			884030H09M065H			6.5m			
1200669927			884030H09M070H			7m			
1200669931			884030H09M075H			7.5m			
1200669932			884030H09M080H			8m			
1200668381			884030H09M100			10m			
5P CABLE H09									
1200668509			885030H09M006			0.6m			
1200668497			885030H09M010			1m			
1200669756			885030H09M015H			1.5m			
1200668500			885030H09M020			2m			
1200669762			885030H09M020H			2m			
1200669757			885030H09M025H			2.5m			
1200668510			885030H09M030			3m			
1200669763			885030H09M030H			3m			
1200668853			885030H09M040			4m			
1200668501			885030H09M050			5m			
1200668854			885030H09M060			6m			
1200668502			885030H09M092			9.2m			
1200668511			885030H09M100			10m			
1200668683			885030H09M150			15m			
1200668684			885030H09M200			20m			
8P CABLE P02									
1200661455			888030P02M005			0.5m			
1200660579			888030P02M010			1m			
1200668803			888030P02M010H			1m			
1200660585			888030P02M100			10m			
1200668807			888030P02M100H			10m			
1200669353			888030P02M130			13m			
1200660586			888030P02M150			15m			
1200668808			888030P02M150H			15m			
1200668327			888030P02M200			20m			
1200668809			888030P02M200H			20m			