


E	1	1	A	0	6	0	1	6	M	X	X	X	X
---	---	---	---	---	---	---	---	---	---	---	---	---	---

H=2 PCS ID CARRIER

L+Tol. (SEE PART LIST)

PIN 1		WHITE/ORANGE		PIN 1
PIN 2		WHITE/GREEN		PIN 2
PIN 3		ORANGE		PIN 3
PIN 4		GREEN		PIN 4

SHIELD CONNECTED TO THE HOUSING



MOLEX PN	ENGINEERING NO	L+Tol.[mm]
1201088438	E11A06016M380	38000
1201088420	E11A06016M010	1000
1201088421	E11A06016M020	2000
1201088422	E11A06016M030	3000
1201088423	E11A06016M040	4000
1201088424	E11A06016M050	5000
1201088425	E11A06016M060	6000
1201088426	E11A06016M080	8000
1201088427	E11A06016M100	10000
1201088428	E11A06016M120	12000
1201088429	E11A06016M150	15000
1201088430	E11A06016M180	18000
1201088431	E11A06016M200	20000
1201088432	E11A06016M230	23000
1201088433	E11A06016M250	25000
1201088434	E11A06016M270	27000
1201088435	E11A06016M300	30000
1201088436	E11A06016M340	34000
1201088437	E11A06016M350	35000
1201088438	E11A06016M380	38000
1201088439	E11A06016M400	40000
1201088440	E11A06016M450	45000

MOLEX PN	ENGINEERING NO	L+Tol.[mm]
1201088441	E11A06016M500	50000
1201088442	E11A06016M550	55000
1201088443	E11A06016M600	60000
1201088444	E11A06016M650	65000
1201088445	E11A06016M700	70000
1201088446	E11A06016M750	75000
1201088447	E11A06016M760	76000
1201088448	E11A06016M800	80000
1201088449	E11A06016M850	85000
1201088506	E11A06016M070	7000
1201088509	E11A06016M420	42000
1201088510	E11A06016M530	53000
1201088511	E11A06016M570	75000
1201088525	E11A06016M900	90000
1201088585	E11A06016M460	46000
1201088586	E11A06016M540	54000
1201088587	E11A06016M610	61000
1201088588	E11A06016M950	95000
1201088763	E11A06016M680	68000
1201088774	E11A06016M003	300
1201088775	E11A06016M006	600
1201088844	E11A06016M002	200

CABLE SPECIFICATION
CONDUCTOR:
MATERIAL: BARE COPPER
SECTION: 0.22mm² - 24AWG
INSULATION:
COMPOUND: PE
DIAMETER: Ø1.20mm
COLOR: WHITE/ORANGE, WHITE/GREEN,
ORANGE, GREEN
JACKET:
COMPOUND: TPU
COLOR: TEAL
DIAMETER: Ø6.5mm

7	1	LABEL	VINYL	YELLOW
6	2	M12 SHIELD SLEEVE	BRASS	Ni-PLATED
5	2	NUT M12 MA HEX SW13	BRASS	Ni-PLATED
4	8	CONTACT 10 MA STA	BRASS	SELECTED GOLD OVER NICKEL
3	2	INSERT M12 MA 4P DC	PUR	BLACK
2	-	OVER MOULD	TPU	BLACK
1	-	CABLE #24-2-2 TEAL WELD SLAG RESIST	TPU	TEAL
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH

LENGTH	TOLERANCE
0m-1m	+40 mm
>1m-5m	+60 mm
>5m-10m	+80 mm
>10m-20m	+140 mm
>20m-30m	+160 mm
>30m	+1% length

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
F E = 0 F E = 0 F E = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex CSE M12 ETH 4P DC MA MA STR WSOR XM DE								
	mm		2:1													
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 689781 DRWN: MDHARMANTI CHK'D: RSILLER APPR: RSILLER			2021/08/03 2021/11/21 2021/11/21								
	ANGULAR TOL ± 1.0°															
DIVISIONAL SYMBOLS	4 PLACES		±		INITIAL REVISION: DRWN: MDHARMANTI APPR: RSILLER			PRODUCT CUSTOMER DRAWING								
	3 PLACES		±													
	2 PLACES		± 0.05													
	1 PLACE		± 0.3													
	0 PLACES		± 0.5													
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												THIRD ANGLE PROJECTION			DRAWING
				A3-SIZE		120108		SEE PART LIST		GENERAL MARKET		1 OF 1				

