



Stubby Screwdriver, #2 Phillips, 1-1/2-Inch Round Shank



Full hollow shaft for work on stacked circuit boards or other long bolt applications. Allows for work in close quarters. Internal flanges provide solid, twist-resistant shaft anchor. Cushion-Grip™ handle allows for greater torque and comfort. Handle end is also color coded for easy identification.

Specifications

| | | | |
|---------------|---------------|------------------|-----------------|
| Tip Type: | Phillips | Magnetic: | No |
| Tip Size: | #2 | Shank Type: | Round |
| Shank Length: | 1.5" (3.8 cm) | Material: | Steel |
| Insulated: | No | Handle Material: | Rubber |
| Handle Color: | Black | Overall Length: | 3.438" (8.7 cm) |
| Weight: | 1.6 oz (45 g) | | |