






FRONT VIEW




STANDARD SCREW & GASKET
Index of protection: IP65





L + Tolerance (see Table on sheet 3)





L + Tolerance (see Table on sheet 3)



DIN Connector views
for PN without LED






DIN Connector views
for PN with LED



Electrical diagram printed in white

ELECTRICAL DIAGRAMS



BILL OF MATERIALS

ITEM	QTY.	DESCRIPTION
14	0/2	I/D CARRIER
13	0/1	LABEL PLASTIC
12	0/1	WASHER
11	0/1	PCB
10	1	GASKET
9	1	SCREW
8	4	CONTACT DIN
7	1	INSERT DIN A
6	-	MOULDING MATERIAL BLACK PP
5	5	CONTACT MALE
4	1	M12 COUPLING NUT MALE
3	1	M12 INSERT 5P MALE
2	-	MOULDING MATERIAL BLACK TPU
1	-	CABLE

DOCUMENT STATUS P1 RELEASE DATE 2024/04/05 09:07:10

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	CURRENT REV DESC: RETRACTED DOCUMENT																														
	<table border="1"> <tr> <th>FUNCTIONAL SYMBOLS</th> <th>DIMENSION UNITS</th> <th>SCALE</th> </tr> <tr> <td>$\nabla_A = 0$</td> <td>mm</td> <td>1:1</td> </tr> <tr> <td>$\nabla_E = 0$</td> <td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td> </tr> <tr> <td>$\nabla_P = 0$</td> <td colspan="2">ANGULAR TOL $\pm 1.0^\circ$</td> </tr> <tr> <td></td> <td>4 PLACES</td> <td>\pm</td> </tr> <tr> <td></td> <td>3 PLACES</td> <td>\pm</td> </tr> <tr> <td></td> <td>2 PLACES</td> <td>± 0.05</td> </tr> <tr> <td></td> <td>1 PLACE</td> <td>± 0.3</td> </tr> <tr> <td></td> <td>0 PLACES</td> <td>± 0.5</td> </tr> </table>	FUNCTIONAL SYMBOLS	DIMENSION UNITS				SCALE	$\nabla_A = 0$	mm	1:1	$\nabla_E = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		$\nabla_P = 0$	ANGULAR TOL $\pm 1.0^\circ$			4 PLACES	\pm		3 PLACES	\pm		2 PLACES	± 0.05		1 PLACE	± 0.3		0 PLACES	± 0.5	EC NO: 782067 DRWN: VISHAH2 CHK'D: RSILLER APPR: RSILLER
FUNCTIONAL SYMBOLS	DIMENSION UNITS	SCALE																														
$\nabla_A = 0$	mm	1:1																														
$\nabla_E = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)																															
$\nabla_P = 0$	ANGULAR TOL $\pm 1.0^\circ$																															
	4 PLACES	\pm																														
	3 PLACES	\pm																														
	2 PLACES	± 0.05																														
	1 PLACE	± 0.3																														
	0 PLACES	± 0.5																														
DIVISIONAL SYMBOLS	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	DRAWING A3-SIZE	SERIES 121035	MATERIAL NUMBER SEE SHEET 3	CUSTOMER GENERAL MARKET	DOCUMENT NUMBER 1210350367	DOC TYPE PSD	DOC PART 000	REVISION B																						

ENGINEERING NO. - NUMERICAL CODE (Available parts see PART LIST table. Others parts available upon request).

OPTIONS

E 8 5 0 X X X X X X X X X X

E=Form A
(18mm
contact
spacing)

8=MMC M12
Connector

5=5 Poles

0=Default Standard Wiring

Cable type:
See Table

Units:
M=Meter

Length
Examples:
005=0.5 units
010=1 units
100=10 units

Electrical configuration:
0 = Without circuit
A = S0 24V Yellow LED
B = C4 24V Yellow LED
C = S0 110V Yellow LED
D = C4 110V Yellow LED
E = S0 24V Green LED
F = C4 24V Green LED
G = S0 110V Green LED
H = C4 110V Green LED
J = S0 24V Red LED
K = C4 24V Red LED
L = S0 110V Red LED
M = C4 110V Red LED
S = C4 230V Yellow LED



DIN Earth Position - o'clock &
M12 connector body:
0 = Earth H6/H12, Male Straight
2 = Earth H6/H12, Male Right Angle

Overmold color:
Blank (Standard)=Black
A=Grey / G=Black / Y=Yellow

Coupling Nut:
Blank (Standard)=Knurled Brass Ni Plated
1=Hexagonal Stainless steel
5=Knurled Derlin
7=Knurled Brass Ni Plated, Teflon Coated
9=Knurled / Hexagonal Brass Ni Plated

H= 2 pcs. of I/D Carrier PVC Transparent
(Cables Ixx & P82 always with
2 pcs. I/D Carrier)

R= NBR Integrated Gasket & Screw (IP67)



CABLE TYPE	NO. OF WIRES	CROSS SECTION	CABLE JACKET	UL	CSA	STATIC: TEMP. / BENDING RADIUS	DYNAMIC: TEMP. / BENDING RADIUS	SHIELD
A23	3	0.75mm ²	PVC BLACK	-	-	-20°C to +70°C, 3xO.D.	-15°C to +70°C, 5xO.D.	-
A58	3	20AWG	PVC BLACK	UL 2661	C22.2 II A 105°C/300V	-30°C to +105°C, 10xO.D.	-5°C to +105°C, 15xO.D.	-
B08	3	18AWG	PUR YELLOW	UL 20668	C22.2 II A 90°C/300V	-	-	-
B31	3	0.50mm ²	WSOR BLACK	UL 21215	-	-	-25°C to +80°C, 7.5xO.D.	-
E12	3	0.50mm ²	PVC BLACK	-	-	-20°C to +70°C, 3xO.D.	-15°C to +70°C, 5xO.D.	-
I12	3	0.50mm ²	CEI PVC GREY	-	-	-25°C to +70°C, 10xO.D.	-5°C to +70°C, 15xO.D.	-
P12	3	0.50mm ²	PUR BLACK	-	-	-40°C to +90°C, 7.5xO.D.	-15°C to +90°C, 12.5xO.D.	-
P82	3	0.34mm ²	PUR IRR ORANGE	-	-	-50°C to +105°C, 5xO.D.	-40°C to +105°C, 7.5xO.D.	-

Over	Up to and including	Tolerance
0	1000	±20
1000	3000	±30
3000	5000	±40
5000	10000	±50
10000	15000	±100
15000	20000	±150
20000		±L/100

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	CURRENT REV DESC: RETRACTED DOCUMENT																											
	<table border="1"> <tr> <th>FUNCTIONAL SYMBOLS</th> <th>DIMENSION UNITS</th> <th>SCALE</th> </tr> <tr> <td>∇/\bar{A} = 0</td> <td>mm</td> <td>1:1</td> </tr> <tr> <td>∇/\bar{E} = 0</td> <td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td> </tr> <tr> <td>∇/\bar{P} = 0</td> <td colspan="2">ANGULAR TOL ± 1.0°</td> </tr> <tr> <td rowspan="5">DIVISIONAL SYMBOLS</td> <td>4 PLACES</td> <td>±</td> </tr> <tr> <td>3 PLACES</td> <td>±</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.05</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.3</td> </tr> <tr> <td>0 PLACES</td> <td>± 0.5</td> </tr> </table>	FUNCTIONAL SYMBOLS	DIMENSION UNITS				SCALE	∇/\bar{A} = 0	mm	1:1	∇/\bar{E} = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		∇/\bar{P} = 0	ANGULAR TOL ± 1.0°		DIVISIONAL SYMBOLS	4 PLACES	±	3 PLACES	±	2 PLACES	± 0.05	1 PLACE	± 0.3	0 PLACES	± 0.5	EC NO: 782067 DRWN: VISHAH2 CHK'D: RSILLER APPR: RSILLER	
FUNCTIONAL SYMBOLS	DIMENSION UNITS	SCALE																											
∇/\bar{A} = 0	mm	1:1																											
∇/\bar{E} = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)																												
∇/\bar{P} = 0	ANGULAR TOL ± 1.0°																												
DIVISIONAL SYMBOLS	4 PLACES	±																											
	3 PLACES	±																											
	2 PLACES	± 0.05																											
	1 PLACE	± 0.3																											
	0 PLACES	± 0.5																											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER																						
DOCUMENT STATUS: P1 RELEASE DATE: 2024/04/05 09:07:10		A3-SIZE	121035	1210350367	PSD	000	B																						

PART LIST

Pos.	Part No.	Engineering No.	Cable Length
1	1210350133	E85000P12M006	0.6m
2	1210350148	E85000P12M020	2m
3	1210350156	E85000P12M010	1m
4	1210350157	E85000P12M030	3m
5	1210350201	E85000E12M010	1m
6	1210350202	E85002P12M015	1.5m
7	1210350207	E85000E12M003	0.3m
8	1210350208	E85000E12M006	0.6m
9	1210350209	E85000P12M003	0.3m
10	1210350210	E85000P82M030	3m
11	1210350242	E85002E12M006	0.6m
12	1210350290	E85000E12M030	3m
13	1210350291	E85000E12M050	5m
14	1210350292	E85000P12M100	10m
15	1210350309	E85002A23M020	2m
16	1210350310	E85002A23M030	3m
17	1210350311	E85002A23M040	4m
18	1210350313	E85000P12M017	1.7m
19	1210350326	E85000P12M050	5m
20	1210350339	E85002P12M020	2m
21	1210350348	E85000P12M015	1.5m
22	1210350349	E85000P12M009	0.9m
23	1210350367	E85000P12M020R	2m
24	1210350368	E85000P12M010R	1m
25	1210360178	E850A0P12M020	2m
26	1210360184	E850B0I12M010	1m
27	1210360186	E850B0I12M020	2m
28	1210360187	E850B0I12M030	3m
29	1210360192	E850B0P12M006	0.6m
30	1210360193	E850B0P12M010	1m
31	1210360194	E850B0P12M015	1.5m
32	1210360195	E850B0P12M020	2m
33	1210360196	E850B0P12M050	5m
34	1210360203	E850B2I12M010	1m
35	1210360206	E850B2I12M050	5m

Pos.	Part No.	Engineering No.	Cable Length
36	1210360208	E850B2P12M006	0.6m
37	1210360209	E850B2P12M010	1m
38	1210360210	E850B2P12M020	2m
39	1210360211	E850B2P12M030	3m
40	1210360212	E850B2P12M050	5m
41	1210360356	E850B0P12M030	3m
42	1210360399	E850B0P12M003	0.3m
43	1210360453	E850B0P12M012	1.2m
44	1210360454	E850B0P12M013	1.3m
45	1210360455	E850B0P12M014	1.4m
46	1210360456	E850B0P12M017	1.7m
47	1210360457	E850B2P12M005	0.5m
48	1210360458	E850D0P12M010	1m
49	1210360491	E850A0A58M010	1m
50	1210360492	E850A0A58M015	1.5m
51	1210360493	E850A0A58M030	3m
52	1210360494	E850A0A58M050	5m
53	1210360495	E850A0A58M100	10m
54	1210360496	E850B2B08M030	3m
55	1210360497	E850B2P12M025G	2.5m
56	1210360498	E850T2I12M010	1m
57	1210360542	E850B0E12M0155	1.5m
58	1210360557	E850B0E12M006	0.6m
59	1210360558	E850B0E12M030	3m
60	1210360559	E850B0E12M050	5m
61	1210360560	E850B0P12M0201	2m
62	1210360574	E850B0E12M020	2m
63	1210360576	E850B2E12M010	1m
64	1210360585	E850A0A58M020	2m
65	1210360586	E850B0A58M020	2m
66	1210360588	E850B0B08M003	0.3m
67	1210360589	E850B0B08M010	1m
68	1210360590	E850B0B08M020	2m
69	1210360593	E850B0P12M040	4m
70	1210360594	E850B0P12M100	10m

Pos.	Part No.	Engineering No.	Cable Length
71	1210360596	E850B2E12M006	0.6m
72	1210360597	E850T2P12M010	1m
73	1210360601	E850K0E12M010	1m
74	1210360627	E850B0E12M010	1m
75	1210360629	E850B2P12M0105	1m
76	1210360650	E850B0P12M006H	0.6m
77	1210360651	E850B2P12M020H	2m
78	1210360658	E850B0A58M006	0.6m
79	1210360659	E850B0A58M015	1.5m
80	1210360667	E850A0A58M070	7m
81	1210360675	E850C0A58M100	10m
82	1210360678	E850B2E12M003	0.3m
83	1210360686	E850A2A58M010	1m
84	1210360694	E850A0A58M006	0.6m
85	1210360696	E85002E12M003	0.3m
86	1210360708	E850B0A23M030	3m
87	1210360709	E850B0A23M050	5m
88	1210360719	E850B2A23M017	1.7m
89	1210360725	E850D0A23M030	3m
90	1210360743	E850B2I12M006	0.6m
91	1210360745	E850B0I12M006	0.6m
92	1210360754	E850A0A58M005	0.5m
93	1210360756	E85002E12M030	3m
94	1210360771	E850A0P12M030	3m
95	1210360772	E850A0P12M040	4m
96	1210360773	E850A0P12M100	10m
97	1210360774	E850A2P12M010	1m
98	1210360775	E850A2P12M015	1.5m
99	1210360776	E850A2P12M020	2m
100	1210360788	E850D0P12M006	0.6m
101	1210360789	E850D0P12M020	2m
102	1210360795	E850A0P12M006	0.6m
103	1210360796	E850C0P12M006	0.6m
104	1210360797	E850A0P12M010	1m
105	1210360798	E850C0P12M010	1m

Pos.	Part No.	Engineering No.	Cable Length
106	1210360799	E850C0P12M020	2m
107	1210360813	E850A0A58M007	0.7m
108	1210360815	E850B0I12M010Y	1m
109	1210360816	E850B0I12M020Y	2m
110	1210360817	E850B0I12M030Y	3m
111	1210360819	E850B0I12M006Y	0.6m
112	1210360821	E850B2P12M015	1.5m
113	1210360844	E850B0P12M021	2.1m
114	1210360845	E850B0P12M024	2.4m
115	1210360846	E850B0P12M027	2.7m
116	1210360847	E850B0P12M058	5.8m
117	1210360848	E850B0P12M080	8m
118	1210360849	E850B0P12M085	8.5m
119	1210360850	E850B0P12M090	9m
120	1210360853	E850B2P12M003	0.3m
121	1210360857	E850B0P12M010H	1m
122	1210360858	E850B0P12M020H	2m
123	1210360893	E850B0B31M006	0.6m
124	1210360894	E850B0B31M010	1m
125	1210360895	E850B0B31M015	1.5m
126	1210360896	E850B0B31M030	3m
127	1210360897	E850B2B31M006	0.6m
128	1210360898	E850B2B31M010	1m
129	1210360899	E850B2B31M015	1.5m
130	1210360900	E850B2B31M030	3m
131	1210360940	E850B0P12M008	0.8m
132	1210360957	E850B0P12M030H	3m
133	1210360959	E850B0P12M010Y	1m
134	1210360970	E850B0P12M010R	1m
135	1210360971	E850B0P12M020R	2m
136	1210361900	E850B0A23M015	1.5m
137			
138			
139			
140			







FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	CURRENT REV DESC: RETRACTED DOCUMENT		 E850 DIN A / MMC 5P MM			
	DIMENSION UNITS: mm SCALE: 1:1	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 1.0° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.05 1 PLACE ± 0.3 0 PLACES ± 0.5					EC NO: 782067 DRWN: VISHAH2 2024/03/26 CHK'D: RSILLER 2024/04/05 APPR: RSILLER 2024/04/05
DIVISIONAL SYMBOLS	INITIAL REVISION:		DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
	DRWN: APAWLAK01 2016/05/30 APPR: RSILLER 2024/04/05		1210350367		PSD	000	B
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
			A3-SIZE	121035	SEE PART LIST	GENERAL MARKET	3 OF 3


Table of length tolerances [mm]		
Over	Up to and including	Tolerance
0	1000	±20
1000	3000	±30
3000	5000	±40
5000	10000	±50
10000	15000	±100
15000	20000	±150
20000		±L/100



PART No MATRIX - PN Key

E	8	5	X	X	X	X	X	X	X	X	X	X	X	X	
E = Form A (18mm contact spacing)	8 = MMC Single Keyway	5=5 Pole	Wiring details: 0 = Positive Switching (pin 3&4) 1 = Negative Switching (pin 1&4)		XXX = Cable Type			M = Metres F = Feet	Length: 020=2 Meters 050=5 Meters 200=20 Meters			Coupling Nut Material: Blank=Standard 1=Stainless Steel 5=Delrin 7=Teflon coat		H=I/D Carrier M12 Overmoulding color: Blank=Black Standard Y=Yellow A=Grey	
				DIN Earth Position - o'clock & M12 connector body: 0 = Earth H6/H12, MALE Straight 2 = Earth H6/H12, MALE 90°		Electrical configuration: 0 = Without LED/Without circuit A = S0 24V Yellow LED B = C4 24V Yellow LED C = S0 110V Yellow LED D = C4 110V Yellow LED E = S0 24V Green LED F = C4 24V Green LED G = S0 110V Green LED H = C4 110V Green LED J = S0 24V Red LED K = C4 24V Red LED L = S0 110V Red LED M = C4 110V Red LED S = C4 230V Yellow LED									

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#515183													
mm		NTS															
GENERAL TOLERANCES (UNLESS SPECIFIED)																	
		MM	INCH	EC NO: 826028 DRWN: SANATK1 2025/06/02 CHK'D: GGA 2025/06/30 APPR: GGA 2025/06/30 INITIAL REVISION: DRWN: JMARSZALEK 2012/11/08 APPR: MIWASIECZKO 2012/11/09 DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													
4 PLACES	±	±	±														
3 PLACES	±	±	±														
2 PLACES	±	±	±														
1 PLACE	±	±	±														
0 PLACES	±	±	±	ANGULAR TOL ± °		FIRST ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
DOCUMENT STATUS		P1	RELEASE DATE	2025/06/30	13:30:36	A3-SIZE		121036		SEE SHEET 3		GENERAL MARKET		1 OF 3			



Cable type

Cable Type	Jacket Material	Jacket Color	Wire cross section	Braid
A23	PVC	Black	0.75mm ²	no
A58	PVC	Black	20AWG	no
B08	PUR	Yellow	18AWG	no
E03	PVC	Black	0.34mm ²	no
E12	PVC	Black	0.5mm ²	no
I12	CEI PVC	Grey	0.5mm ²	no
P12	PUR	Black	0.5mm ²	no
P82	PUR IRR	Orange	0.34mm ²	no
S26	PVC	Yellow	0.34mm ²	yes
B31	PUR	Black	0.5mm ²	no

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE	CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#515183				
mm	NTS					
GENERAL TOLERANCES (UNLESS SPECIFIED)				E85XXXXXXXXXX DIN A + CORDSETS M12		
				PRODUCT CUSTOMER DRAWING		
				DOCUMENT NUMBER	DOC TYPE	DOC PART
				SD-121036-001	PSD	001
				REVISION	C1	
				SHEET NUMBER		
				2 OF 3		

EC NO: 826028
 DRWN: SANATK1 2025/06/02
 CHK'D: GGA 2025/06/30
 APPR: GGA 2025/06/30

INITIAL REVISION:
 DRWN: JMARSZALEK 2012/11/08
 APPR: MIWASIECZKO 2012/11/09

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

FIRST ANGLE PROJECTION

DRAWING A3-SIZE

SERIES 121036

MATERIAL NUMBER SEE SHEET 3

CUSTOMER GENERAL MARKET

PART LIST

Pos.	Molex PN:	Engineering No.:
1	1210350133	E85000P12M006
2	1210360178	E850A0P12M020
3	1210360192	E850B0P12M006
4	1210360193	E850B0P12M010
5	1210360194	E850B0P12M015
6	1210360195	E850B0P12M020
7	1210360196	E850B0P12M050
8	1210360209	E850B2P12M010
9	1210360211	E850B2P12M030
10	1210360356	E850B0P12M030
11	1210360399	E850B0P12M003
12	1210360491	E850A0A58M010
13	1210360492	E850A0A58M015
14	1210360493	E850A0A58M030
15	1210360494	E850A0A58M050
16	1210360495	E850A0A58M100
17	1210360497	E850B2P12M025G
18	1210360559	E850B0E12M050
19	1210360574	E850B0E12M020
20	1210360593	E850B0P12M040
21	1210360594	E850B0P12M100
22	1210360596	E850B2E12M006
23	1210360627	E850B0E12M010
24	1210360694	E850A0A58M006
25	1210360708	E850B0A23M030
26	1210360719	E850B2A23M017
27	1210360725	E850D0A23M030
28	1210360754	E850A0A58M005
29	1210360789	E850D0P12M020
30	1210360813	E850A0A58M007
31	1210360816	E850B0I12M020Y
32	1210360817	E850B0I12M030Y
33	1210360821	E850B2P12M015
34	1210360847	E850B0P12M058
35	1210361900	E850B0A23M015
36		
37		
38		
39		
40		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#515183					
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 826028		2025/06/02		E85XXXXXXXXX	
				DRWN: SANATK1		2025/06/30		DIN A + CORDSETS M12	
				CHK'D: GGA		2025/06/30		PRODUCT CUSTOMER DRAWING	
				APPR: GGA		2025/06/30			
1 PLACE ± ±				INITIAL REVISION:		DOCUMENT NUMBER		DOC TYPE	
0 PLACES ± ±				DRWN: JMARSZALEK		2012/11/08		DOC PART	
ANGULAR TOL ± °				APPR: MIWASIECZKO		2012/11/09		REVISION	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		FIRST ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	
				A3-SIZE		121036		CUSTOMER	
				SEE SHEET 3		GENERAL MARKET		SHEET NUMBER	
								3 OF 3	

DOCUMENT STATUS	P1	RELEASE DATE	2025/06/30	13:30:36
-----------------	----	--------------	------------	----------