





NOTE:

- 1) MATERIAL: SEE TABLE
- 2) FINISHES: SEE TABLE
- 3) FLAG LABEL IS MARKED WITH PART No., DATE CODE, VOLTAGE AND AMPERAGE
- 4) ELECTRICAL DATA
POLE: 4
MAX. VOLTAGE: IEC60664 600V
UL2237 600V
MAX. CURRENT: 25A
- 5) ENVIRONMENTAL PROTECTION: IP67
TEMPERATURE RATING: -20C TO 90C
- 6) PACKAGING:
ASSEMBLIES ARE BAGGED SEPARATELY IN POLY BAGS WITH BAR CODE LABEL ATTACHED TO OUTSIDE OF BAG
- 7) ASSEMBLY IS RoHS COMPLIANT
- 8) CERTIFICATION
UL2237
- 9) ADDITIONAL CABLE INFORMATION
MINIMUM BEND RADIUS: 7.5X CABLE DIAMETER (0.656")
- 10) DIMENSIONS ARE REFERENCE UNLESS OTHERWISE SPECIFIED

WIRING DIAGRAM



PART NUMBER MATRIX

334T30K26M005A3

CABLE TYPE
12/4C AWG TYPE
SHIELDED

FINISH LENGTH
M005 = 0.5 METER
M010 = 1 METER
M100 = 10 METER





CHART	PART NO.	ENGINEERING NO.	FINISHED LENGTH
	1300620300	334T30K26M020A3	2.0M (78.7")
	1300611064	304T06K26M040A3	4.0M (157.5")
	1300611065	304T06K26M060A3	6.0M (236.2")

11	WARNING LABEL	VINYL	MULTI COLOR
10	WRAP LABEL	VINYL	YELLOW
9	FEMALE COUPLING NUT	BRASS	NICKEL PLATED
8	4P FEMALE INSERT	TPE	BLACK
7	SOCKET SLEEVE	STAINLESS STEEL	
6	SOCKET CONTACT	BRASS	GOLD PLATED
5	OVER MOLD	TPE	GRAY
4	MALE COUPLING NUT	BRASS	NICKEL PLATED
3	4P MALE INSERT	TPE	BLACK
2	PIN CONTACT	BRASS	GOLD PLATED
1	12/4C AWG SHIELDED, VFD	TPE JACKET, XLPE INSUL	BLACK
ITEM	DESCRIPTION	MATERIAL	FINISH

CABLE LENGTH TOLERANCES
>.3M [1FT]: +19mm-0 [+1.75in-0]
.3 - .9M [1 - 3FT]: +44.5mm-0 [+1.75in-0]
1.8 - 3.7M [6 - 12FT]: +88.9mm-0 [+3.50in-0]
3.7 - 7.3M [12 - 24FT]: +165.1mm-0 [+6.50in-0]
7.3-14.6M [24 - 48FT]: +317.5mm-0 [+12.50in-0]
14.6 - 30.5M [48-100FT]: +622.3mm-0 [+24.50in-0]
OVER 30M [100FT] +2% OF FINISHED LENGTH


QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
= 0	ADD CABLE INFO EC NO: 176042 DRWN: MZIELINSKI CHKD: CCHRASTKA APP: BWOODMAN REV		GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION UNITS		SCALE									
= 0					HYBRID		1:1									
= 0					DRWN BY		DATE									
= 0					CHK'D BY		DATE									
= 0					APPR BY		DATE									
= 0	B2		B		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER					
= 0					DRAWING SIZE				130062		SEE CHART					
					B				DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER	
									1300620300		PSD		000		1 OF 1	



NOTE:

- 1) MATERIAL: SEE TABLE
- 2) FINISHES: SEE TABLE
- 3) FLAG LABEL IS MARKED WITH PART No., DATE CODE, VOLTAGE AND AMPERAGE
- 4) ELECTRICAL DATA
POLE: 4
MAX. VOLTAGE: IEC60664 600V
UL2237 600V
MAX. CURRENT: 25A
- 5) ENVIRONMENTAL PROTECTION: IP67
TEMPERATURE RATING: -20C TO 90C
- 6) PACKAGING:
ASSEMBLIES ARE BAGGED SEPARATELY IN POLY BAGS WITH BAR CODE LABEL ATTACHED TO OUTSIDE OF BAG
- 7) ASSEMBLY IS RoHS COMPLIANT
- 8) CERTIFICATION
UL2237
- 9) ADDITIONAL CABLE INFORMATION
MINIMUM BEND RADIUS: 7.5X CABLE DIAMETER (0.656")
- 10) DIMENSIONS ARE REFERENCE UNLESS OTHERWISE SPECIFIED

WIRING DIAGRAM



PART NUMBER MATRIX

334T30K26M005A3

CABLE TYPE
12/4C AWG TYPE
SHIELDED

FINISH LENGTH
M005 = 0.5 METER
M010 = 1 METER
M100 = 10 METER




CHART	PART NO.	ENGINEERING NO.	FINISHED LENGTH
	1300620300	334T30K26M020A3	2.0M (78.7")
	1300611064	304T06K26M040A3	4.0M (157.5")
	1300611065	304T06K26M060A3	6.0M (236.2")

11	WARNING LABEL	VINYL	MULTI COLOR
10	WRAP LABEL	VINYL	YELLOW
9	FEMALE COUPLING NUT	BRASS	NICKEL PLATED
8	4P FEMALE INSERT	TPE	BLACK
7	SOCKET SLEEVE	STAINLESS STEEL	
6	SOCKET CONTACT	BRASS	GOLD PLATED
5	OVER MOLD	TPE	GRAY
4	MALE COUPLING NUT	BRASS	NICKEL PLATED
3	4P MALE INSERT	TPE	BLACK
2	PIN CONTACT	BRASS	GOLD PLATED
1	12/4C AWG SHIELDED, VFD	TPE JACKET, XLPE INSUL	BLACK
ITEM	DESCRIPTION	MATERIAL	FINISH

CABLE LENGTH TOLERANCES
>.3M [1FT]: +19mm-0 [+ .75in-0]
.3 - .9M [1 - 3FT]: +44.5mm-0 [+1.75in-0]
1.8 - 3.7M [6 - 12FT]: +88.9mm-0 [+3.50in-0]
3.7 - 7.3M [12 - 24FT]: +165.1mm-0 [+6.50in-0]
7.3-14.6M [24 - 48FT]: +317.5mm-0 [+12.50in-0]
14.6 - 30.5M [48-100FT]: +622.3mm-0 [+24.50in-0]
OVER 30M [100FT] +2% OF FINISHED LENGTH

QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
= 0	ADD CABLE INFO EC NO: 176042 DRWN: MZIELINSKI CHKD: CCHRASTKA APP: BWOODMAN REV		GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION UNITS		SCALE									
= 0					HYBRID		1:1									
= 0					DRWN BY		DATE									
= 0					TWOLEDGEGBRIE		2016/07/08									
= 0					CHK'D BY		DATE									
= 0					KCOX01		2016/11/09		APPR BY		DATE		PRODUCT CUSTOMER DRAWING			
= 0	BWOODMAN		2016/11/14		DRAWING SIZE		THIRD ANGLE PROJECTION									
= 0	B				SERIES		MATERIAL NUMBER		CUSTOMER							
= 0	B2		REV		130062		SEE CHART		DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER	
						1300620300		PSD		000		1 OF 1				