

MATERIALS AND FINISHES:

SMA JACK STR CONNECTOR:

BODY, CRIMP TUBE, JAM NUT: BRASS
PLATED GOLD

CENTER CONTACT: BERYLLIUM COPPER
PLATED GOLD

INSULATOR: TEFLON

LOCK WASHER: PHOSPHOR BRONZE
PLATED GOLD

GASKET: SILICONE RUBBER

CONNECTOR:

MHF® I LK

MATED HEIGHT: 2.90MM MAX



CABLE: 1.32MM CABLE BLACK

NOTES:


PACKAGING BY PLASTIC BAG

PERFORMANCE REQUIRMENTS:

1. FREQUENCY: DC~ 6GHz
2. IMPEDANCE: 50 OHMS
3. TEST 100% CONTINUITY
4. TEST 100% HI-POT: AC 350 V@0.5mA



0732306206	2.559±.118	65.00±3.00
0732306205	2.000±.118	50.80±3.00
0732306204	4.000±.197	101.60±5.00
0732306203	6.000±.197	152.40±5.00
0732306202	8.000±.197	203.20±5.00
0732306201	10.000±.197	254.00±5.00
0732306200	12.087±.236	307.00±6.00
PART No.	IN	MM
	A	



RECOMMENDED MOUNTING HOLE

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
	DIMENSION UNITS		SCALE		CURRENT REV DESC: ADD NEW P/N: 0732306206			molex CA, SMA JACK STR BKHD IP68 TO MHF® I LK WITH 1.32MM CABLE EWR#15294-D		