





NOTES:

- MATERIALS:
CONTACT: BERYLLIUM COPPER
FERRULE: BRASS
INSULATOR: PEI
ALL OTHER METAL PARTS: STAINLESS STEEL
- FINISH:
CONTACT & FERRULE: GOLD
ALL OTHER METAL PARTS: PASSIVATED
- ELECTRICAL:
IMPEDANCE: 50Ω
FREQUENCY RANGE: DC TO 40GHz
VSWR: 1.30 MAX

MOLEX P/N: 0732520300

FUNCTIONAL SYMBOLS $\frac{F}{A} = 0$ $\frac{F}{C} = 0$ $\frac{F}{P} = 0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										CURRENT REV DESC: FIXED BARREL THREAD SPEC CALL OUT WAS M4x0.5-6g NOW M4.5x0.5-6g. FIXED RECOMMENDED CABLE STRIP DIM WAS .205[5.20] NOW .209[5.30].										molex 2.92mm FEMALE BULKHEAD FOR .086 CABLE EWR-16564-A																																																
	DIMENSION UNITS					SCALE																																																															
	INCH/MM					NTS																																																															
	GENERAL TOLERANCES (UNLESS SPECIFIED)																																																																				
						MM					INCH																																																										
	4 PLACES					±					±																																																										
	3 PLACES					± 0.1000					±																																																										
	2 PLACES					± 0.200					±																																																										
	1 PLACE					± 0.30					±																																																										
	0 PLACES					±					±																																																										
ANGULAR TOL										± 5°																																																											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										FIRST ANGLE PROJECTION 										DRAWING C-SIZE										SERIES 73252										MATERIAL NUMBER 0732520300										CUSTOMER										SHEET NUMBER 1 OF 1									