



LTCC SURFACE MOUNT

Low Pass Filter

LFCG-2275+

50Ω DC to 2275 MHz

THE BIG DEAL


- Insertion Loss, Typ. 0.9 dB
- Stopband Rejection, Typ. 48 dB
- Passband Return Loss, Typ. 15 dB
- 0805 Surface Mount Footprint
- Power Handling: 4.5 Watts



Generic photo used for illustration purposes only

APPLICATIONS

- ISM Applications
- Communications, Radar, and Defense Systems
- Test and Measurement Equipment
- LTE & 5G MIMO Infrastructure

FUNCTIONAL DIAGRAM**PRODUCT OVERVIEW**

Mini-Circuits' LFCG-2275+ is a miniature low temperature co-fired ceramic (LTCC) low pass filter with a DC to 2275 MHz passband supporting a variety of applications. This model provides 0.9 dB typical insertion loss over a wide band due to its rugged monolithic construction. Housed in an 0805 ceramic form factor which is ideal for dense signal chain PCB layouts where it complements MMIC size and performance. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well suited for environmental extremes of high humidity and temperature.

KEY FEATURES

Features	Advantages
Ultra-wide Stopband	The LTCC lowpass filter provides a very good stopband rejection until 10 GHz suitable for wide band applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Small Size, 0805	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Rugged Power Handling, 4.5 Watts	Handles up to 4.5 Watts in a small 0805 package.



LTCC SURFACE MOUNT

Low Pass Filter

LFCG-2275+

50Ω DC to 2275 MHz

ELECTRICAL SPECIFICATIONS^{1,2,3} AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	DC-F1	DC - 2275	—	0.9	2.0
	Freq. Cut-Off ⁴	F _c	2700	—	3.0	—
	Return Loss	DC-F1	DC - 2275	—	15	—
Stopband	Rejection	F ₂ -F ₃	3300 - 4000	20	45	—
		F ₃ -F ₄	4000 - 7000	35	48	—
		F ₄ -F ₅	7000 - 10000	—	25	—

1. Tested in Evaluation Board P/N TB-LFCG-2275+.

2. This filter is bi-directional, RF1 and RF2 ports may be interchanged. See S-Parameters for actual performance.

3. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.


4. Typical variation ± 5%.

ABSOLUTE MAXIMUM RATINGS⁵

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power ⁶	4.5 W @ +25°C

5. Permanent damage may occur if any of these limits are exceeded.

6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 1 W at +125°C.

TYPICAL FREQUENCY RESPONSE AT +25°C








LTCC SURFACE MOUNT

Low Pass Filter

LFCG-2275+

50Ω DC to 2275 MHz

TYPICAL PERFORMANCE GRAPHS

**Mini-Circuits®**



LTCC SURFACE MOUNT

Low Pass Filter

LFCG-2275+

50Ω DC to 2275 MHz




FUNCTIONAL DIAGRAM

Figure 1. LFCG-2275+ Functional Diagram

CASE STYLE DRAWING

METALLIZATION

Weight: .008 grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$ **SUGGESTED PCB LAYOUT (PL-429)****NOTES:**

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" $\pm .001$ ". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Figure 2. Suggested PCB Layout PL-429

PRODUCT MARKING*: VZ

*Marking may contain other features or characters for internal lot control.

Mini-Circuits



LTCC SURFACE MOUNT

Low Pass Filter

LFCG-2275+

50Ω DC to 2275 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD.**CLICK HERE**

Performance Data and Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	GE0805C-2 Lead Finish: Tin over Nickel plating
RoHS Status	Compliant
Tape and Reel	F114
Suggested Layout for PCB Design	PL-429
Evaluation Board	TB-LFCG-2275+
	Gerber File
Environmental Rating	ENV126

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Mini-Circuits®