











Recommended torque 7-10 in-lbs

CABLE ASSEMBLY INSTRUCTIONS

NOTES:

- MATERIALS:
CONTACT & LOCK RING: BERYLLIUM COPPER
FERRULE: BRASS
INSULATOR: PEI
ALL OTHER METAL PARTS: STAINLESS STEEL
- FINISH:
CONTACT & FERRULE: GOLD
LOCK RING: ALBALOY
ALL OTHER METAL PARTS: PASSIVATED
- ELECTRICAL:
IMPEDANCE: 50Ω
FREQUENCY RANGE: DC TO 40GHz
VSWR: 1.30 MAX

MOLEX P/N: 0732520310

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
F_A = 0 F_C = 0 F_P = 0 DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: UPDATED TOLERANCE BLOCK						
	INCH/MM		NTS								
	GENERAL TOLERANCES (UNLESS SPECIFIED)				molex 2.92mm MALE FOR .047 CABLE EWR16564-A						
		MM	INCH								
	4 PLACES		±		±	PRODUCT CUSTOMER DRAWING					
	3 PLACES		±	0.1000	±						
	2 PLACES		±	0.200	±	DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
	1 PLACE		±	0.30	±	732520310		PSD	000	A1	
	0 PLACES		±		±	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
ANGULAR TOL		±	5°								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		FIRST ANGLE PROJECTION		DRAWING	SERIES	0732520310				1 OF 1	
				C-SIZE	73252						