



Recommended torque 7-10 in-lbs
CABLE ASSEMBLY INSTRUCTIONS

NOTES:

1. MATERIALS:
 CONTACT & LOCK RING: BERYLLIUM COPPER
 FERRULE: BRASS
 INSULATOR: PEI
 ALL OTHER METAL PARTS: STAINLESS STEEL
2. FINISH:
 CONTACT & FERRULE: GOLD
 LOCK RING: ALBALOY
 ALL OTHER METAL PARTS: PASSIVATED
3. ELECTRICAL:
 IMPEDANCE: 50Ω
 FREQUENCY RANGE: DC TO 50GHz
 VSWR: 1.35 MAX

MOLEX P/N: 0733870160

FUNCTIONAL SYMBOLS $F_A = 0$ $F_C = 0$ $F_P = 0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
	DIMENSION UNITS	SCALE	
	INCH/MM	NTS	
	GENERAL TOLERANCES (UNLESS SPECIFIED)		
		MM	INCH
	4 PLACES ±	±	
	3 PLACES ± 0.1000	±	
	2 PLACES ± 0.200	±	
	1 PLACE ± 0.30	±	
	0 PLACES ±	±	
	ANGULAR TOL ±	5°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			
FIRST ANGLE PROJECTION			
DRAWING			
SERIES			
C-SIZE 73387			
CURRENT REV DESC: UPDATED TOLERANCE BLOCK			
STATUS: Production			
DRWN: James Borrelli 2024-10-07			
CHK'D: Alex Robertson 2024-10-10			
APPR: Kevin Tagan 2024-10-10			
PRODUCT CUSTOMER DRAWING			
DOCUMENT NUMBER			
733870160			
DOC TYPE			
PSD			
DOC PART			
000			
REVISION			
A1			
MATERIAL NUMBER			
0733870160			
CUSTOMER			
SHEET NUMBER			
1 OF 1			