









73412-3150	TAPE AND REEL (DU 40000 PCS)
PART NO.	PACKAGING

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC: EWR-16884-C			
		mm/INCH		NTS					
		GENERAL TOLERANCES (UNLESS SPECIFIED)							
		ANGULAR TOL ± 0.5°							
		4 PLACES		±					
3 PLACES		±		STATUS: Production DRWN: JasonYS Su CHK'D: Darry Cheng APPR: Darry Cheng					
2 PLACES		±							
1 PLACE		±							
0 PLACES		±							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION						DRAWING	
				C-SIZE		73412		CUSTOMER	
								SHEET NUMBER	
								1 OF 4	




RECOMMENDED FOOTPRINT PATTERN




CONNECTOR ON RECOMMENDED FOOTPRINT PATTERN

NOTE
4. NO GROUND, SIGNAL, RESIST IN THIS AREA.






MASK THICKNESS: $t = 0.12$

METAL MASK



REFLOW TEMPERATURE PROFILE
SENJU METAL INDUSTRY CO., LTD. : M705-SHF(Sn96.5 Ag3.0 Cu0.5)


FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
F_A = 0		DIMENSION UNITS	SCALE	CURRENT REV DESC: EWR-16884-C				molex				
F_C = 0		mm/INCH	NTS									
F_P = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)										
DIVISIONAL SYMBOLS		ANGULAR TOL ± 0.5°						MCRF RECEPTACLE VERTICAL MCRF-J,EWR-16884-A				
		4 PLACES	±									
		3 PLACES	±									
		2 PLACES	±									
		1 PLACE	±	PRODUCT CUSTOMER DRAWING								
		0 PLACES	±						DOCUMENT NUMBER			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
				C-SIZE		73412						2 OF 4
				STATUS: Production		DRWN: JasonYS Su	2024-12-31	734123150		PSD	000	A
				CHK'D: Darry Cheng		APPR: Darry Cheng	2025-01-17					
							2025-01-17					





- ## NOTES

1. EMBOSS TAPE : PS, T=0.3
2. TOP TAPE: PET
3. REEL:PS
4. PACKING LABEL
5. TAPING SPECIFICATION FOLLOWS JIS C 0806 (IEC 60286-3).
6. MAKE EMPTY SECTION OF LEADER AND END ON EACH END OF THE TAPE.
7. TOP TAPE SHALL NOT STICK OUT FROM EMBOSS TAPE.
8. TOP TAPE SHALL NOT COVER FEED HOLE.


FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
F_A = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: EWR-16884-C					molex				
	mm/INCH		NTS											
	GENERAL TOLERANCES (UNLESS SPECIFIED)													
	ANGULAR TOL ± 0.5°													
	4 PLACES ±													
DIVISIONAL SYMBOLS	3 PLACES ±		STATUS: Production DRWN: JasonYS Su CHK'D: Darry Cheng APPR: Darry Cheng					2024-12-31 2025-01-17 2025-01-17						
	2 PLACES ±													
	1 PLACE ±													
	0 PLACES ±													
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													
THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER			SHEET NUMBER			
		C-SIZE		73412							3 OF 4			
						504123150								




P/N: 73412-3150



5000 SET PER TAPE



5000 SET PER 15" REEL



40000 SET PER OUTER CARTON BOX
P/N: 89499-9032

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
= 0 = 0 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: EWR-16884-C			molex MCRF RECEPTACLE VERTICAL MCRF-J,EWR-16884-A									
	mm/INCH		NTS														
	GENERAL TOLERANCES (UNLESS SPECIFIED)																
ANGULAR TOL ± 0.5°				STATUS: Production DRWN: JasonYS Su 2024-12-31 CHK'D: Darry Cheng 2025-01-17 APPR: Darry Cheng 2025-01-17				PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER 734123150 DOC TYPE PSD DOC PART 000 REVISION A									
4 PLACES		±															
3 PLACES		±															
2 PLACES		±															
1 PLACE		±															
DIVISIONAL SYMBOLS	0 PLACES		±		PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER 734123150 DOC TYPE PSD DOC PART 000 REVISION A												
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION					DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
								C-SIZE		73412						4 OF 4	