



MMIC SURFACE MOUNT

# Monolithic Amplifier

RAM-7+

50Ω DC to 2 GHz

## FEATURES

- Wideband, DC to 2 GHz
- Cascadable Ceramic Package
- Internally Matched to 50Ω
- Excellent Repeatability
- Aqueous Washable
- Protected Under US Patent 6,943,629



Generic photo used for illustration purposes only

CASE STYLE: AF190

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications



## APPLICATIONS

- Cellular
- UHF/VHF
- Communication Systems
- Transmission Receivers

## PRODUCT OVERVIEW

RAM-7+ (RoHS compliant) is a wideband amplifier offering high dynamic range. It has repeatable performance from lot to lot. It is enclosed in a ceramic surface-mount package. RAM-7+ uses Darlington configuration and is fabricated using InGaP HBT technology. Expected MTBF is 3,700 years at +100°C case temperature.

## SIMPLIFIED SCHEMATIC AND PIN DESCRIPTION



Function	Pin Number	Description
RF-IN	1	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.
RF-OUT and DC-IN	3	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit".
GND	2,4	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.

REV. E  
ECO-024944  
RAM-7+  
MCL NY  
250320

**Mini-Circuits**

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 1 OF 4



MMIC SURFACE MOUNT

# Monolithic Amplifier

RAM-7+

50Ω DC to 2 GHz

**ELECTRICAL SPECIFICATIONS AT +25°C AND 22 mA UNLESS NOTED OTHERWISE**

Parameter	Conditions (GHz)	Min.	Typ.	Max.	Units
Frequency Range <sup>1</sup>		DC		2	GHz
Gain	0.1		13.5		
	1		12.5		
	2	8.5 <sup>2</sup>	11		dB
Input Return Loss	DC - 2		9.5		dB
Output Return Loss	DC - 2		11		dB
Output Power @ 1 dB Compression	1		+5.5		dBm
Output IP3	1		+19		dBm
Noise Figure	1		4.5		dB
Recommended Device Operating Current			22		mA
Device Operating Voltage			+4.0		V
Device Voltage Variation vs. Temperature at 22 mA			-2.3		mV/°C
Device Voltage Variation vs. Current at +25°C			15.1		mV/mA
Thermal Resistance, Junction-to-Case <sup>3</sup>			155		°C/W

1. Guaranteed specification DC-2 GHz. Low frequency cut off determined by external coupling capacitors.

2. Full temperature range.

3. Case is defined as ground leads.

**ABSOLUTE MAXIMUM RATINGS**

Parameter	Ratings
Operating Temperature	-54°C to +100°C
Storage Temperature	-65°C to +150°C
Operating Current	60 mA
Power Dissipation	275 mW
Input Power	+13 dBm

Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation.




MMIC SURFACE MOUNT

# Monolithic Amplifier

RAM-7+

50Ω DC to 2 GHz


## RECOMMENDED APPLICATION CIRCUIT



Test Board includes case, connectors, and components (in bold) soldered to PCB

R BIAS	
Vcc	"1%" Res. Values (Ohms) for Optimum Biasing
7	137
8	182
9	226
10	274
11	316
12	365
13	412
14	453
15	499

## PRODUCT MARKING



Markings in addition to model number designation may appear for internal quality control purposes.



MMIC SURFACE MOUNT

# Monolithic Amplifier

RAM-7+

50Ω DC to 2 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. [CLICK HERE](#)

Performance Data & Graphs	<a href="#">Data Table</a> <a href="#">Swept Graphs</a> <a href="#">S-Parameter Data Set (.zip file)</a>
Case Style	AF190 Ceramic surface-mount, 0.083 body diameter
Suggested Layout for PCB Design	PL-254
Evaluation Board	TB-414-7+
Environmental Ratings	ENV08T6

## ESD RATING

Human Body Model (HBM): Class 1B (500 V to < 1000 V) in accordance with ANSI/ESD STM 5.1 - 2001  
Machine Model (MM): Class M1 (<100 V) in accordance with ANSI/ESD STM 5.2 - 1999

## NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)