

Sensing Lite Loose Tube, Gel-Filled, Single-Jacket, Single-Armored Cable 24 F, Single-mode (OS2)

CORNING

Part Number:
024EUC-T4101ASN

Corning Sensing Lite single-jacket, single-armored cables are lightweight, reduced-diameter, armored cables designed for direct-buried, duct and aerial (lashed) installation. The loose tube design provides stable performance over a wide temperature range and is compatible with any telecommunications-grade optical fiber.

Features and Benefits

Flexible, craft-friendly buffer tubes

Facilitate easy routing in closures

SZ-stranded, loose tube design


Isolates fibers from installation and environmental rigors and facilitates mid-span access

Dielectric central strength member


No preferential bend and requires no bonding or grounding

Polyethylene jacket

Rugged, durable and easy to strip (while providing superior protection against UV radiation, fungus, abrasion and other environmental factors)



Sensing Lite Loose Tube, Gel-Filled, Single-Jacket, Single-Armored Cable, 24 F, Single-mode (OS2)



Sensing Lite Loose Tube, Gel-Filled, Single-Jacket, Single-Armored Cable, 24 F, Single-mode (OS2)

Sensing Lite Loose Tube, Gel-Filled, Single-Jacket, Single-Armored Cable 24 F, Single-mode (OS2)

CORNING

Specifications

General Specifications

Installation Methods	Aerial, Direct Buried
Cable Type	Loose Tube
Environment	Outdoor
Product Type	Dielectric armor
Fiber Category	Single-mode (OS2)
Cable geometry	Round

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	USDA Rural Development Programs
Design and Test Criteria	Telcordia GR-20, ICEA-640

Environmental Conditions

Temperature Range, Installation	-30 °C to 70 °C (-22 °F to 158 °F)
Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)
Temperature Range, Storage	-40 °C to 70 °C (-40 °F to 158 °F)

Cable Design

Central Element	Dielectric
Fiber Count	24
Number of Ripcords	2
Outer Jacket Color	Black
Outer Jacket Material	Polyethylene (PE)
Tensile Strength Elements and/or Armoring - Layer 1	Corrugated steel tape armor
Buffer Tube Color	Blue, Orange
Buffer Tube Diameter	2.5 mm (0.1 in)

Sensing Lite Loose Tube, Gel-Filled, Single-Jacket, Single-Armored Cable 24 F, Single-mode (OS2)

CORNING

Cable Design

Number of Active Tubes	2
Number of Filling Elements	4
Number of Tube Positions	6
Tape	Water-swellable
Tape, Layer 1	Water-swellable
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Fibers per Tube	12
Color Code Standards	Telcordia

Mechanical Specifications

Max. Tensile Strength, Long-Term	890 N (200.08 lbf)
Max. Tensile Strength, Short-Term	2700 N (606.98 lbf)
Nominal Outer Diameter	12.1 mm (0.48 in)
Min. Bend Diameter Installation	364 mm (14.33 in)
Min. Bend Diameter Operation	242 mm (9.53 in)

Optical Characteristics

Fiber Code	E
Performance Option Code	01
Fiber Category	OS2
Fiber Type	Single-mode (OS2) / 250 µm
Fiber Name	Single-mode (OS2)
Maximum Attenuation	0.4 dB/km / 0.4 dB/km / 0.3 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Compliance	ITU-T G.652.D

Sensing Lite Loose Tube, Gel-Filled, Single-Jacket, Single-Armored Cable 24 F, Single-mode (OS2)



Dimensions	
Cable Weight	136 kg/km (91.39 lb/1000 ft)



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.