





TYS4020330M-10

PHYSICAL DIMENSIONS:


A	4.00	± 0.20
B	4.00	± 0.20
C	2.00	MAX.
D	1.20	± 0.30
E	1.60	± 0.30



LAND PATTERNS FOR REFLOW SOLDERING



RECOMMENDED SOLDERING CONDITIONS



ELECTRICAL SPECIFICATION

	Min	Nom	Max
INDUCTANCE (uH) L @ 100 KHz/1V ± 20%	26.4	33.0	39.6
DCR (Ω)	0.550	0.715	

Saturation Current(A)	0.85
SRF (MHz)	11
Temperature Rise Current (A)	0.49

NOTES: UNLESS OTHERWISE SPECIFIED

- OPERATING TEMPERATURE RANGE: -40°C TO +125°C (INCLUDING SELF-HEATING) .
- STORAGE TEMPERATURE RANGE (PACKAGING CONDITIONS): -10°C TO +40°C AND RH 70% (MAX.)
- UNLESS OTHERWISE SPECIFIED, THE STANDARD ATMOSPHERIC CONDITIONS FOR MEASUREMENT/TEST AS:
 - AMBIENT TEMPERATURE: 20±15°C.
 - RELATIVE HUMIDITY: 65%±20%.
- DEFINITION OF SATURATION CURRENT (ISAT): DC CURRENT AT WHICH THE INDUCTANCE DROPS ≤30% FROM ITS VALUE WITHOUT CURRENT.
- DEFINITION OF TEMPERATURE RISE CURRENT (IRMS): DC CURRENT THAT CAUSES THE TEMPERATURE RISE ($\Delta T \leq 40^\circ\text{C}$) FROM 20°C AMBIENT.

DIMENSIONS ARE IN mm .			This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.		Laird		
C	CHANGE DIMENSIONS:D/E	01/11/18	QIU	TYS4020330M-10	REV C	PART TYPE: POWER INDUCTOR	DRAWN BY: QIU
B	CHANGE LOGO	08/06/15	QIU	DATE: 09/06/12	SCALE: NTS	SHEET:	
A	ORIGINAL DRAFT	09/06/12	QIU	CAD #: TYS4020330M-10-C	TOOL #		1 of 1
REV	DESCRIPTION	DATE	INT				