

SIZE	TENSILE STRENGTH(N/mm ²)
TX-30	~116






© 2013 Essentra Components. All rights reserved.
Registered in England, Company No. 547495.
Registered Office: Essentra plc
Langford Locks, Kidlington, Oxford, OX5 1HX


Condition of Sale can be found on our website: essentra.com.

Essentra Components does not warrant that the files will be error free and may create new versions ("Upgrades") at any time, which may correct such errors. Essentra Components has no obligation to notify you of such upgrades. Any upgraded file will be published to the website, when it becomes available.

You are not permitted to load any of the files on to a network server for the purposes of distribution to one or more other computer(s) on that network or to effect such distribution. Essentra Components shall not be liable for any loss or damage whatsoever or however caused, arising directly or indirectly from the use of the files.

UNCONTROLLED COPY



STATUS		APPROVED DRAWING	
UNLESS OTHERWISE STATED			
ALL DIMENSIONS IN mm		DO NOT SCALE	
LINEAR TOLERANCE		THIRD ANGLE PROJECTION	
SIZE	(0)	(0.0)	(0.00)
0-10	±0.5	±0.15	±0.10
>10-30	±0.5	±0.20	±0.15
>30-50	±0.5	±0.30	±0.20
>50-100	±0.8	±0.50	±0.25
>100-200	±1.5	±0.80	±0.40
>200-300	±2.0	±1.20	±0.80
>300-500	±3.0	±2.00	±1.00
>500	±5.0	±3.00	±1.50
			
		ANGULAR TOLERANCE ±0.5 DEGREES	
		UNSPECIFIED RADII 0.25mm	
		DRAFT ANGLE 0.5 DEGREES	
		DIMENSIONS IN PARENTHESIS () ARE FOR REFERENCE ONLY	
ITEM CODE		CREATE	
20820558		Jul 22 2025 00:00 AM	
LEGACY CODE		MATERIAL	
		PEEK	
		COLOUR	
		LIGHT BROWN	
		FINISH	
		-	
TITLE:			
M6X30 TORX PAN HEAD SCREW			
-			
DWG. No.		SCALE	ISSUE
		3:1	1
		SHEET	1 of 2

SIZE	TENSILE STRENGTH(Lbf/in²)
TX-30	~16824






© 2013 Essentra Components. All rights reserved.
Registered in England, Company No. 547495.
Registered Office: Essentra plc
Langford Locks, Kidlington, Oxford, OX5 1HX

Condition of Sale can be found on our website: essentra.com.

Essentra Components does not warrant that the files will be error free and may create new versions ("Upgrades") at any time, which may correct such errors. Essentra Components has no obligation to notify you of such upgrades. Any upgraded file will be published to the website, when it becomes available.

You are not permitted to load any of the files on to a network server for the purposes of distribution to one or more other computer(s) on that network or to effect such distribution. Essentra Components shall not be liable for any loss or damage whatsoever or however caused, arising directly or indirectly from the use of the files.

UNCONTROLLED COPY



STATUS		APPROVED DRAWING																																					
UNLESS OTHERWISE STATED		DO NOT SCALE																																					
ALL DIMENSIONS IN inches		THIRD ANGLE PROJECTION																																					
LINEAR TOLERANCE <table border="1"> <thead> <tr> <th>SIZE</th><th>(0.00)</th><th>(0.000)</th><th>(0.0000)</th></tr> </thead> <tbody> <tr> <td>0 - 0.394</td><td>±0.020</td><td>±0.006</td><td>±0.004</td></tr> <tr> <td>>0.394 - 1.181</td><td>±0.020</td><td>±0.008</td><td>±0.006</td></tr> <tr> <td>>1.181 - 1.969</td><td>±0.020</td><td>±0.012</td><td>±0.008</td></tr> <tr> <td>>1.969 - 3.937</td><td>±0.031</td><td>±0.020</td><td>±0.010</td></tr> <tr> <td>>3.937 - 7.874</td><td>±0.059</td><td>±0.031</td><td>±0.016</td></tr> <tr> <td>>7.874 - 11.811</td><td>±0.079</td><td>±0.047</td><td>±0.031</td></tr> <tr> <td>>11.811 - 19.685</td><td>±0.118</td><td>±0.079</td><td>±0.039</td></tr> <tr> <td>>19.685</td><td>±0.197</td><td>±0.118</td><td>±0.059</td></tr> </tbody> </table>		SIZE	(0.00)	(0.000)	(0.0000)	0 - 0.394	±0.020	±0.006	±0.004	>0.394 - 1.181	±0.020	±0.008	±0.006	>1.181 - 1.969	±0.020	±0.012	±0.008	>1.969 - 3.937	±0.031	±0.020	±0.010	>3.937 - 7.874	±0.059	±0.031	±0.016	>7.874 - 11.811	±0.079	±0.047	±0.031	>11.811 - 19.685	±0.118	±0.079	±0.039	>19.685	±0.197	±0.118	±0.059		
SIZE	(0.00)	(0.000)	(0.0000)																																				
0 - 0.394	±0.020	±0.006	±0.004																																				
>0.394 - 1.181	±0.020	±0.008	±0.006																																				
>1.181 - 1.969	±0.020	±0.012	±0.008																																				
>1.969 - 3.937	±0.031	±0.020	±0.010																																				
>3.937 - 7.874	±0.059	±0.031	±0.016																																				
>7.874 - 11.811	±0.079	±0.047	±0.031																																				
>11.811 - 19.685	±0.118	±0.079	±0.039																																				
>19.685	±0.197	±0.118	±0.059																																				
		ANGULAR TOLERANCE ±0.5 DEGREES UNSPECIFIED RADII 0.25mm DRAFT ANGLE 0.5 DEGREES DIMENSIONS IN PARENTHESES () ARE FOR REFERENCE ONLY																																					
ITEM CODE	20820558	CREATE	JUL 22 2025 00:00 AM																																				
LEGACY CODE		MATERIAL	PEEK																																				
		COLOUR	LIGHT BROWN																																				
		FINISH	-																																				
TITLE:																																							
M6X30 TORX PAN HEAD SCREW																																							
-																																							
DWG. No.	20820558	SCALE	3:1																																				
		SHEET	1																																				
			2 of 2																																				