






RUBBER PART GENERAL TOLERANCE				
PART DIM.	1	2	(3)	
0 TO 3	± 0.2	± 0.3	± 0.4	
3 TO 6	± 0.2	± 0.4	± 0.5	
6 TO 10	± 0.3	± 0.5	± 0.6	
10 TO 18	± 0.3	± 0.6	± 0.8	
18 TO 30	± 0.4	± 0.8	± 1.0	
30 TO 50	± 0.5	± 1.0	± 1.5	
50 TO 80	± 0.6	± 1.2	± 2.0	
80 TO 120	± 0.7	± 1.4	± 2.5	
120 TO 180	± 0.8	± 1.6	± 3.0	
180 TO 250	± 1.0	± 2.0	± 4.0	
250 TO 315	± 1.2	± 2.5	± 5.0	
315 TO 400	± 1.5	± 3.0	± 6.0	
400 TO 500	± 1.8	± 3.5	± 7.0	
500 OVER	± 0.4 %	± 0.8 %	± 1.5 %	



SEC. A-A



98.03.25	NEW	C98-3282	M.O
LET	DATE	REVISION RECORD	NO. CHKD

GENERAL TOLERANCE									
10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT	MASS		
A ±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1			
B ±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1			
C ±0.3	±0.5	±0.8	±1.4	±2	±30'	0.45			
SPECIFIED CLASS-3							MASS		
SEE RUBBER PART GENERAL TOLERANCE							(35.0) g		

CUSTOMER		MATERIAL SPEC.		TREAT. & FIN.	
CUSTOMER PART NO.		CUSTOMER DWG NO.		NAME	
OFFICE		TRIAL PART NO.		GROMMET (LICENSE LAMP)	
VENDOR		VENDOR NO.			
DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
R	NEW	98.03.25	mm	2/1	3
APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	
小野	米(典)木村	YAMAZAKI	OSADA		
98.03.25	98.03.25	98.03.25	92.07.16	98.03.25	
PART NO.		7035-6203		SET DWG NO.	
CH. CODE		7035-6203:R			
DWG NO.		YAZAKI CORPORATION			