

| PART NO.                 | W1   | W2   | H1     | H2     | MATL. & SPEC. | APPLICABLE WIRE SIZE |
|--------------------------|------|------|--------|--------|---------------|----------------------|
| 7116-1230<br>(7B16-1230) | 2.60 | 4.20 | (2.70) | (3.70) | Sn PLATING    | 0.3 ~ 0.5 Sq         |
| 7116-1231                | 3.30 | 5.00 | (3.60) | (4.50) | Sn PLATING    | 0.85 ~ 2 Sq          |
| 7116-1230-08             | 2.60 | 4.20 | (2.70) | (3.70) | Au PLATING    | 0.3 ~ 0.5 Sq         |
| 7116-1231-08             | 3.30 | 5.00 | (3.60) | (4.50) | Au PLATING    | 0.85 ~ 2 Sq          |

注 記




1) かん合継端子品番: 7114-1230 ETC.

2) ( ) 内品番は、エア-バツダ (A/B) 回路及び特別  
管理回路に使用する時に適用すること。

NOTES

1) MATING MALE TERMINAL NO. : 7114-1230 ETC.

2) PART NUMBERS IN PARENTHESIS SHALL BE USED  
FOR AIR BAG (A/B) CIRCUITS AND OTHER CIRCUITS  
DESIGNATED FOR SPECIAL MONITORING.



電線圧着後被覆部形状 (参考)

SEC. A-A

|                   |          |                 |        |          |        |          |        |                   |            |                  |          |                              |       |
|-------------------|----------|-----------------|--------|----------|--------|----------|--------|-------------------|------------|------------------|----------|------------------------------|-------|
|                   |          |                 |        |          |        | CUSTOMER |        |                   |            | MATERIAL SPEC.   |          | TREAT. & FIN.                |       |
| Δ                 | 11.10.26 | ADDED VIEW ETC. |        | C11-Z814 |        | K. U     |        | CUSTOMER PART NO. |            | CUSTOMER DWG NO. |          | Δ BRASS (t=0.3)              |       |
| Δ                 | 93.10.14 | ADDED PART NO.  |        | C93-7035 |        | M. K     |        |                   |            |                  |          | NAME AS TYPE TERMINAL FEMALE |       |
|                   | 89.02.07 | NEW             |        | C89-L257 |        | T. M     |        | OFFICE            |            | TRIAL PART NO.   |          | -----                        |       |
| LET               | DATE     | REVISION RECORD |        | NO.      |        | CHKD     |        | VENDOR            |            |                  |          |                              |       |
| GENERAL TOLERANCE |          |                 |        |          |        |          |        |                   |            |                  |          |                              |       |
|                   | 10MAX    | 50MAX           | 100MAX | 250MAX   | 2500VR | ANGLE    | ECCENT | DWG TYPE          | DWG SOURCE | DWG DATE         | UNIT     | SCL                          | ANGLE |
| A                 | ±0.15    | ±0.2            | ±0.3   | ±0.5     | ±0.75  | ±30'     | 0.1    | R                 | NEW        | 89.02.18         | mm       | 5/1                          | 3     |
| B                 | ±0.2     | ±0.3            | ±0.55  | ±0.95    | ±1.4   | ±30'     | 0.1    | APPROVED          | CHECKED    | CHECKED          | DESIGN   | DRAWN                        |       |
| ⊙                 | ±0.3     | ±0.5            | ±0.8   | ±1.4     | ±2     | ±30'     | 0.15   | M. KASHIYAMA      |            |                  | ISHIZUKA | K. URANO                     |       |
| SPECIFIED         |          |                 |        |          |        |          |        | MASS              |            | 9                |          | 11.10.26                     |       |
|                   |          |                 |        |          |        |          |        |                   |            |                  |          | YAZAKI CORPORATION           |       |