




△ PART NO. AND CH. CODE	APPLICABLE WIRE SIZE	W ¹	H ¹	W	H	TREATMENT
7116-1232	0.3~0.85	5.60	5.10	2.20	2.20	Sn PLATING
7116-1233	1.25~2	6.00	5.60	3.60	3.60	Sn PLATING
7116-1232-08	0.3~0.85	5.60	5.10	2.20	2.20	NOTE 2
7116-1233-08	1.25~2	6.00	5.60	3.60	3.60	NOTE 2



SEC. A-A

SEC. B-B

SEC. C-C





注記

- △ 1. 対応品番: 7114-1232 ETC., 7114-1233 ETC.
- △ 2. 対応品番は ⑤ 部とする。(7116-1232-08, 7116-1233-08)

△ NOTES

- 1. MATING PART NO.: 7114-1232 ETC., 7114-1233 ETC.
- 2. THE INSIDE OF AREA ⑤ SHALL BE GOLD PLATING. (7116-1232-08, 7116-1233-08)



△ 1. 3. 07. 02 ADDED GENERAL TOLERANCE, ETC. C13-Z297	R. M	CUSTOMER PART NO.	CUSTOMER DWG NO.	MATL. BRASS	TREAT. SEE TABLE	ISSUE MARK
△ 8. 10. 25 添記訂正	8MC-1432	OFFICE	TRIAL PART NO.	SPEC. t=0.30	NAME W TYPE TERMINAL (F)	
△ 8. 01. 20 差機大図作成及び品番追加	8MC-0124	VENDOR				
LET DATE	REVISION RECORD	NO.	CHKD			
△ GENERAL TOLERANCE						
A 10MAX 50MAX 100MAX 250MAX 250OVR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT
A ±0.15 ±0.2 ±0.3 ±0.5 ±0.75 ±30'	0.1		R	NEW	88.01.20	mm 5:1 3
B ±0.2 ±0.3 ±0.5 ±0.95 ±1.4 ±30'	0.1		APPROVED	CHECKED	DESIGN	DRAWN
C ±0.3 ±0.5 ±0.8 ±1.4 ±2 ±30'	0.15		M. KASHIYAMA		SAKAI	R. MAIERANO
SPECIFIED MASS						
13.07.02 84.06.20 13.07.02						
YAZAKI CORPORATION						