





PART NO. AND CH. CODE	△L ₄	H ₁	H ₂	W ₁	R ₁	W ₂	R ₂	WIRE SIZE (mm ²)
7116-4110-02.△	16.60	△(2.45)	△(3.55)	2.30	0.45	2.80	0.45	△0.3~0.6 OR EQUIVALENT
7116-4111-02.△	16.60	△(3.25)	△(4.45)	3.00	0.65	3.60	0.65	△0.75~1.25 OR EQUIVALENT
7116-4112-02.△	16.60	△(4.00)	△(5.50)	3.70	0.85	4.60	0.90	△1.5~3.0 OR EQUIVALENT
△7116-4113-02	18.50	(5.40)	(7.05)	4.90	1.10	6.50	1.50	3.0~5.0 OR EQUIVALENT

注 記

- △ 1. 嵌合相手品番: 7114-4110-02 ETC.
- △ 2. 7116-4113-02 についての通電流値は、2.5 mm²電線相当以下とする。
- △ 3. 7116-4113-02 に 5 mm²電線を圧着して使用する場合には、専用ハウジングが必要となります。

NOTES

- △ 1. MATING PART NO.: 7114-4110-02 ETC.
- △ 2. CURRENT FOR 7116-4113-02 SHALL BE THE
CURRENT FOR 2.5 mm² WIRE OR UNDER.
- △ 3. IN CASE 5 mm² WIRE IS CRIMPED WITH THE
TERMINAL 7116-4113-02, SPECIAL HOUSING
IS REQUIRED.



LET	DATE	REVISION RECORD	NO.	CHKD
△	07.06.04	CHANGED WIRE SIZE	C07-Z475	M. M
△	03.07.10	CHANGED WIRE SIZE	C03-X452	K. O
△	99.10.11	ADDED NOTE	C99-7134	T. S
△	99.02.17	ADDED PART NO. ETC.	C99-L407	Y. U
△	97.09.26	CHANGED FORM ETC.	△ C97-N033	H. K
△	95.07.25	NEW	C95-M194	Y. U

GENERAL TOLERANCE			
10MAX	50MAX	100MAX	250MAX
10MAX	50MAX	100MAX	250MAX
A	±0.15	±0.2	±0.3
B	±0.2	±0.3	±0.55
C	±0.3	±0.5	±0.8
SPECIFIED			

A B	
CUSTOMER	
CUSTOMER PART NO.	CUSTOMER DWG NO.
OFFICE	
TRIAL PART NO.	
VENDOR	

SEC. A-A		SEC. B-B		ISSUE MARK	
MATL: COPPER ALLOY		t=0.3		TREAT.	
SPEC: (TIN PLATING)				& FIN.	
NAME		2. 8 SYSTEM CONNECTOR			
		FEMALE TERMINAL			

YAZAKI CORPORATION
3