


PART NO.	W ₁	W ₂	(H ₁)	(H ₂)	APPLICABLE WIRE SIZE
7116-4765-02	2.60	3.30	2.84	3.69	CAVS 0.85 ~ CAVS 1.25 AVSS 0.75f ~ AVSS 1.25f
7116-4766-02	2.20	2.85	2.30	3.16	CAVS 0.3 ~ CAVS 0.5 AVSS 0.3f ~ AVSS 0.5f

注記

1. 相手端子品番 : 7114-4660-02 ETC.

NOTE

1. MATING PARTS NO. : 7114-4660-02 ETC.



SEC. A-A

SEC. B-B

ISSUE MARK

01.09.14		NEW	C01-X870	S. K	OFFICE	CUSTOMER PART NO.		CUSTOMER DWG NO.	
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR	TRIAL PART NO.			
GENERAL TOLERANCE									
10MAX		50MAX	100MAX	250MAX	2500V	ANGLE	ECCENT	DWG. TYPE	DWG. SOURCE
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	加藤 隆	杉山(要)
SPECIFIED		MASS		9		01.09.17		01.09.17	01.09.17
1		2		3		00.09.05		01.09.14	
YAZAKI CORPORATION									

MATL. COPPER ALLOY t=0.25 TREAT. & FIN.

NAME 0.64 TERMINAL FEMALE (太物電線用)

PART NO. 7116-4765-02 ETC.

DWG NO. 7116-4765-02:R SET DWG NO.