



SEC. A-A



RUBBER PART GENERAL TOLERANCE			
PART DIM.	1	2	③
0 TO 3	± 0.2	± 0.3	± 0.4
3 TO 6	± 0.2	± 0.4	± 0.5
6 TO 10	± 0.3	± 0.5	± 0.6
10 TO 18	± 0.3	± 0.6	± 0.8
18 TO 30	± 0.4	± 0.8	± 1.0
30 TO 50	± 0.5	± 1.0	± 1.5
50 TO 80	± 0.6	± 1.2	± 2.0
80 TO 120	± 0.7	± 1.4	± 2.5
120 TO 180	± 0.8	± 1.6	± 3.0
180 TO 250	± 1.0	± 2.0	± 4.0
250 TO 315	± 1.2	± 2.5	± 5.0
315 TO 400	± 1.5	± 3.0	± 6.0
400 TO 500	± 1.8	± 3.5	± 7.0
500 OVER	± 0.4 %	± 0.8 %	± 1.5 %

注記

1. 適用電線サイズ : 標準仕上り外径 Ø2.00~Ø2.20 とする。

NOTE

1. APPLICABLE WIRE SIZE : NOMINAL DIAMETER OF FINISHED
CABLE Ø2.00~Ø2.20

ISSUE MARK

				CUSTOMER				MATL. SILICONE RUBBER		TREAT. & FIN.	
				CUSTOMER PART NO.				SPEC. (GRAY)			
				OFFICE				NAME		090 II 5mm pitch RUBBER	
				VENDOR						STOPPER (M SIZE)	
				VENDOR NO.				PART NO.		7158-3004-40	
				DWG TYPE				CH. CODE			
				DWG SOURCE				DWG NO.		7158-3004-40:R	
				DWG DATE						YAZAKI CORPORATION	
				UNIT							
				SCL							
				ANGLE							
				APPROVED							
				CHECKED							
				DESIGN							
				DRAWN							
				MAEDA							
				SAMUKAWA							
				95.10.20							
				94.09.27							
				95.10.23							

1

2

3