

1

2




3

△ TABLE 1

SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	MATERIAL	COLOR	QTY.
7283-1062 ETC.	①	SEE TABLE 2	△ HPA	SEE TABLE 2	1
	②	7157-4098	△ HPA	NATURAL	1

TABLE 2

SUB ASSEMBLY PART NO. AND CH. CODE	PART NO. AND CH. CODE	COLOR
7283-1062.△	7183-1062	NATURAL
7283-1062-10.△	7183-1062-10	DARK GRAY
7283-1062-30.△	7183-1062-30	BLACK
7283-1062-40.△	7183-1062-40	LIGHT GRAY
7283-1062-50.△	7183-1062-50	ORANGE
△ 7283-1062-60.△	7183-1062-60	GREEN
△ 7283-1062-80.△	7183-1062-80	BROWN
7283-1062-90.△	7183-1062-90	BLUE






注記

1. 適用端子品番: 7116-4020 ETC.

NOTE

1. APPLICABLE TERMINAL NO.: 7116-4020 ETC.

ISSUE MARK

								CUSTOMER						MATL. SPEC. SEE TABLE 1				TREAT. & FIN.	
								CUSTOMER PART NO.				CUSTOMER DWG NO.				NAME Δ 2. 3II (090II) 6P CONNECTOR SUB ASSEMBLY FEMALE			
Δ	05/02/10	CHANGED MATERIAL. Δ	C05-Z220	T. H				OFFICE				TRIAL PART NO.							
	90/11/10	NEW	C90-M210	M. H				VENDOR											
LET	DATE		REVISION RECORD		NO.	CHKD	VENDOR NO.												
GENERAL TOLERANCE																			
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO. 7283-1062 ETC.					
A	± 0.15	± 0.2	± 0.3	± 0.5	± 0.75	$\pm 30'$	0.1	R	NEW	90/11/10	mm	2:1	3	CH. CODE					
B	± 0.2	± 0.3	± 0.55	± 0.95	± 1.4	$\pm 30'$	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		DWG NO. 7283-1062:R		SET DWG NO.			
$\odot$	± 0.3	± 0.5	± 0.8	± 1.4	± 2	$\pm 30'$	0.15					Y. OHTA K. REYES		YAZAKI CORPORATION					
SPECIFIED						MASS						05.02.11 05.02.10 05.02.10 89/03/15 05/02/10							